



**Catalog Number:** XD7NM-TB  
**Product ID:** 7TAD013840R0015  
**UPC Number:** 78620984422  
**Status:** A



2-1/2 Inch XD Non-Metallic Expansion/Deflection Coupling with Neoprene Rubber Boot and Stainless Steel Clamps

- For use with schedule 40 & 80 PVC rigid conduit to couple sections of conduit & protect wiring systems from damage due to movement.
- Suitable for wet location

Actual



Representative

**North American Specifications (UNSPSC)**

UNSPSC	39131707 Electrical conduit coupling
IGCC	5548 Electrical conduit coupling
Type	XD Expansion/Deflection Couplings
Special Features	Accommodates Axial Expansion/contraction Up to 3/4 Inch, Parallel Deflection Up to 3/4 Inch and Angular Misalignment Up to 30 Degree.
Application	Bridges, Tunnels, Inter-Building Walkways, Docks and Piers and Wastewater and Water Treatment Facilities
Standard	cULus, CSA C22.2 No. 85, UL E23018
Trade Size	2-1/2 in
Material	PVC

**European Specifications (ETIM)**

ETIM	EC000939 Coupler for installation tubes
Material	Plastic
Material quality	PVC
Model	Thread
Two piece	N
With inspection opening and cover	N

**Packaging**

Outer Quantity	1
Outer Dimensions (inches)	12.25x6x6
Weight Uom	4.08 lbs. Each

**Documents / Support Tools**

Technical Drawing / Data Sheet	TDS000230
--------------------------------	-----------