



Representative



Representative

Catalog Number: XPLFL112
Product ID: 7TAD013340R0001
UPC Number: 78620988429
EAN Number: 05415022259810
Status: A

1/2 Inch x 12 Inch XP Flex Explosion Proof Flexible Coupling

- UL Listed for use in hazardous and wet locations.
- Corrosion-resistant, ideal for washdown areas.
- Flexible bronze construction with arc-resistant inner sleeve and brass fittings.
- Terminated with two threaded female end fittings and male close nipples.
- No bonding jumper required.
- Flexible design allows for use to make tight bends or allow for movement or vibration.

North American Specifications (UNSPSC)

UNSPSC	39131707 Electrical conduit coupling
IGCC	5548 Electrical conduit coupling
Type	XP Flex Explosion-Proof Flexible Couplings-Hazardous Location
Special Features	No Bonding Jumper Required
Application	Explosion-Proof and Dust-Ignition-Proof for Use In Hazardous Locations
Standard	UL E193396, cULus
Trade Size	1/2 in
Length	12 in
Material	Brass
Color	Metallic

European Specifications (ETIM)

ETIM	EC000939 Coupler for installation tubes
Material	Metal
Material quality	Other
Model	Thread
Two piece	N
With inspection opening and cover	N

Packaging

Outer Quantity	1
Outer Dimensions (inches)	12x2x2
Weight Uom	1.92 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000382
--------------------------------	------------

Header

3D Model	Available on Website
----------	----------------------