



Actual



Representative

Catalog Number: YLS-7.9-200BC
Product ID: 7TCG009420R0122
UPC Number: 78621074930
EAN Number: 05414363072867
Status: A

Ball-Lock 316 Stainless Steel Cable Tie, Black Polyester Coating, for Temperatures up to 150 Degrees Celsius for Indoor and Outdoor Applications, Length of 200mm (7.87 Inches), Width of 7.9mm (0.311 Inches), Thickness of 0.36mm (0.01 Inches), Tensile Strength Rating of 440 Newtons (100 Pounds)

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5046 Stainless Steel Ties
Type	Stainless Steel
Special Features	Black Polyester Coated
Application	For Temperatures up to 150 Degrees Celsius for Indoor and Outdoor Applications
Width	0.311 in ; 7.9 mm
Length	7.87 in ; 200 mm
Thickness	0.014 in ; 0.36 mm
Material	316 Stainless Steel
Color	Black
Lock Mechanism	Ball-Lock
Tensile Strength	100 pounds ; 440 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	7.9mm
Length belt/tape/tie	200mm
Tie thickness	0.36mm
Max. bundle diameter	50mm
Min. holding force	440N
Operating temperature	-80-+150°C
Model	Internal toothing
Band closure	Ball latch
Material	Metal
Material quality	Stainless steel 316 (V4A)
Surface protection	Plastic-coated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	N
UL approval	N

Packaging

Inner Quantity	100
Inner Dimensions (inches)	10x5.9x.6
Outer Quantity	2500
Outer Dimensions (inches)	11x5.9x9.4
Weight Uom	3.75 lbs. per 1000

