





Tilt Wall Mount for 37" to 70" TVs and Monitors

MODEL NUMBER: DWT3770X



Low-profile mount hangs a flat-panel television, monitor or other display on the wall. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants. Tilts to provide optimal viewing angles.

Description

The VESA-compliant DWT3770X Tilt Wall Mount allows you to mount your flat-panel television, monitor or other display on the wall. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants, it fits most flat-panel displays from 37 to 70 inches. A -10° to 0° tilt capability minimizes glare and provides comfortable viewing from multiple angles.

Low-profile mount is concealed behind the display to give a sleek, professional appearance. Frame is open for easy wall access. Mounting rails adjust horizontally to compensate for off-center wall studs. Built-in bubble level allows accurate display leveling. Durable all-metal frame with scratch-resistant powder-coated finish supports up to 200 pounds. Mounting hardware included. Conforms to VESA-compliant displays with any of the following mounting hole patterns: 200 x 200 mm, 200 x 300 mm, 200 x 400 mm, 300 x 200 mm, 300 x 300 mm, 300 x 400 mm, 400 x 200 mm, 400 x 300 mm, 400 x 400 mm, 500 x 300 mm, 500 x 400 mm, 600 x 300 mm, 600 x 400 mm, 800 x 300 mm and 800 x 400 mm

Features

Mounts Your TV or Monitor to the Wall Fits most flat-panel televisions, monitors and other displays from 37 to 70 in. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants. Mounts out of sight behind display for sleek, professional appearance. Mounting hardware included.

Convenient One-Touch Adjustment -10° to 0° tilt capability provides comfortable viewing from multiple angles. Improves viewing angles in applications where audience is below the display.

Durable Metal Construction Supports up to 200 lb. Open frame allows easy wall access. Adjustable mounting rails compensate for off-center wall studs. Built-in bubble level for accurate display leveling. Scratch-resistant powder-coated finish.

VESA Compliance Supports the following VESA mounting hole patterns: 200 x 200 mm, 200 x 300 mm, 200 x 400 mm, 300 x 200 mm, 300 x 300 mm, 300 x 400 mm, 400 x 200 mm, 400 x 300 mm, 400 x 400 mm, 500 x 300 mm, 500 x 400 mm, 600 x 300 mm, 600 x 400 mm, 800 x 300 mm and 800 x 400 mm

Specifications

OVERVIEW

Highlights

- Fits most flat-panel displays from 37 to 70 in.
- Hangs out of sight for a sleek, professional appearance
- -10° to 0° tilt capability for comfortable viewing
- Supports up to 200 lb.

Package Includes

- DWT3770X Tilt Wall Mount for 32" to 70" TVs and Monitors
- (4) M5 x 14 screws
- (4) M6 x 14 screws
- (4) M6 x 30 screws
- (4) M8 x 20 screws
- (4) M8 x 30 screws
- (4) Washers
- (8) Small spacers
- (4) Big spacers
- (6) Anchor bolts
- (6) Concrete anchors
- (6) D6 washers
- Owner's manual



UPC Code	037332183613
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
Degrees of Motion	-10/+0 Tilt
Distance from Wall (cm)	5
Distance from Wall (in.)	1.77
Distance from Wall (mm)	45
Material of Construction	Steel
Maximum Screen Size (cm)	177.8
Maximum Screen Size (in.)	70
Maximum Weight Capacity (kg)	91
Maximum Weight Capacity (lbs.)	200
Minimum Screen Size (cm)	93.98
Minimum Screen Size (in.)	37
Motion	Tilt
Mounting Location	Wall
Number of Displays	1
Shipping Dimensions (hwd / cm)	21.34 x 6.60 x 88.90
Shipping Dimensions (hwd / in.)	8.40 x 2.60 x 35.00
Shipping Weight (kg)	3.26
Shipping Weight (lbs.)	7.18
Unit Dimensions (hwd / cm)	44 x 86 x 4.77
Unit Dimensions (hwd / in.)	17.32 x 34.02 x 1.88
Unit Weight (kg)	3.29
Unit Weight (lbs.)	7.26
VESA Pattern (mm)	200x200; 200x300; 200x400; 300x200; 300x300; 300x400; 400x200; 400x300; 400x400; 500x300; 500x400; 600x300; 600x400; 800x300; 800x400
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
SPECIAL FEATURES	
Cord Management	No
Security Lock	No



STANDARDS & COMPLIANCE	
Approvals	RoHS3, REACH
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

[https:// products/product-certification-agencies](https://products.product-certification-agencies)