

## Cat6 Gigabit Snagless Molded Patch Cable (RJ45 M/M) - Green, 25-ft.

MODEL NUMBER: N201-025-GN



### Description

With Tripp Lite's new category 6 molded patch cables you can stay ahead of the game by using this high-speed cable to distribute data, voice and video. These cables deliver stable performance up to 550MHz. Each comes UL verified meets EIA/TIA Cat6 TIA/EIA-568-B-2.1 draft 9 standards. Constructed with high-quality copper wire and a staggered-pin plug design, near-end crosstalk levels are kept to a minimum. Designed for use in category 6, category 5e and category 5 applications. Cat6 cables are available in a variety of colors with a snagless boot preventing cable snags.

### Features

- Meets category 6 cabling standards
- Premium cabling for category 6, category 5e and category 5 applications
- Length: 25-ft. Color: green. Connectors: RJ45 male.
- Drastically reduce impedance and structural return loss compared to standard 100MHz wire
- High-quality copper wire and a staggered-pin plug design to keep near-end crosstalk levels to a minimum
- Feature molded connectors with integral strain relief
- Snagless design protects the locking tabs on the RJ45 connectors from being damaged or snapped off during installation
- PVC 4-pair solid UTP
- Deliver stable performance up to 550MHz/1 Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 6 draft 11)
- Available in other colors and lengths

## Specifications

### Highlights

- Meets Category 6 cabling standards
- Drastically reduce impedance and structural return loss compared to standard 100MHz wire
- High-quality copper wire and a shortened body plug design
- Feature molded connectors with integral strain relief
- Snagless boots protect the locking tabs on the RJ45 connectors from being damaged during installation

### System Requirements

- For 1000 Base-T (1Gbps Ethernet), 10/100 Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring TYPE 3 applications as well as EIA/TIA applications

### Package Includes

- 25-ft. Cat6 Green Gigabit Patch Cord Snagless Molded



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

| <b>OVERVIEW</b>                      |  |
|--------------------------------------|--|
| UPC Code                             | 037332099990                                       |
| <b>INPUT</b>                         |  |
| Cable Length (ft.)                   | 25   |
| Cable Length (m)                     | 7.6  |
| <b>PHYSICAL</b>                      |  |
| Wire Gauge (AWG)                     | 24   |
| Shipping Dimensions (hwd / in.)      | 11.000 x 7.000 x 0.500                             |
| Shipping Dimensions (hwd / cm)       | 27.94 x 17.78 x 1.27                               |
| Shipping Weight (lbs.)               | 0.7000   |
| Shipping Weight (kg)                 | 0.32   |
| Color                                | Green  |
| <b>CONNECTIONS</b>                   |  |
| Side A - Connector 1                 | RJ45 (MALE)  |
| Side B - Connector 1                 | RJ45 (MALE)  |
| <b>FEATURES &amp; SPECIFICATIONS</b> |  |
| Technology                           | Cat6   |
| <b>CERTIFICATIONS</b>                |  |
| Certifications                       | RoHS-Compliant                                     |
| Approvals                            | EIA/TIA Cat6 TIA/EIA- 568-B-2.1, draft 9 standards |
| <b>WARRANTY</b>                      |  |
| Product Warranty Period (Worldwide)  | Lifetime limited warranty                          |

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>