

## Cat6 Gigabit Snagless Molded Slim UTP Patch Cable (RJ45 M/M), Blue, 3 ft.

MODEL NUMBER: N201-S03-BL



Connects network components like printers, computers, copiers, routers, servers, modems and switches. Ideal for high-density data centers. Slim design increases airflow in tight spaces.

### Description

The N201-S03-BL Cat6 Gigabit Snagless Molded Slim UTP Patch Cable is perfect for connecting network components like printers, computers, copiers, routers, servers, modems and switches in high-density data centers. Designed for fast transmission and excellent signal quality, this three-foot blue cable ensures peak performance throughout your local area network (LAN).

Manufactured from 28 AWG copper wire, the four-pair stranded UTP N201-S03-BL delivers speeds up to Cat6 Gigabit/1 Gbps. Protected by a PVC jacket, this cable is more than 38% smaller in diameter than standard Cat6 cable, which increases airflow in tight spaces and makes it easier to install around corners and through cable management panels.

RJ45 male connectors guarantee an accurate signal transfer. The snagless design protects the locking tabs against being damaged or broken off during installation. Integral strain relief ensures the cable and connectors last a long time.

### Features

#### Perfect Solution for Your Networking Needs

- Ideal for connecting components like printers, computers, copiers, routers, servers, modems and switches in high-density data centers
- Designed for fast transmission and excellent signal quality
- Ensures peak performance throughout your LAN
- Delivers speeds up to Cat6 Gigabit

#### Special Slim Design

### Highlights

- Over 38% slimmer than standard Cat6 cables
- Rated for Cat6 Gigabit/1 Gbps communications
- Snagless RJ45 male connectors
- Easy to route through cable management panels
- High-quality 28 AWG copper wire

### Package Includes

- N201-S03-BL Cat6 Gigabit Snagless Molded Slim UTP Patch Cable (RJ45 M/M), 3 ft.



- More than 38% smaller in diameter than standard Cat6 cable
- Increases airflow in tight spaces
- Extra flexible for installing around corners and through cable management panels

#### Premium Construction for Superior Performance

- Made from 28 AWG copper wire
- PVC 4-pair stranded UTP
- RJ45 male connectors
- Integral strain relief for long life

#### Snagless Connectors

- Molded snagless boots prevent locking tabs from damage

## Specifications

OVERVIEW	
UPC Code	037332193056
INPUT	
Cable Length (ft.)	3
Cable Length (m)	0.9
PHYSICAL	
Wire Gauge (AWG)	28
Shipping Dimensions (hwd / in.)	9.000 x 7.000 x 0.500
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.0600
Shipping Weight (kg)	0.03
Color	Blue
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
FEATURES & SPECIFICATIONS	
Technology	Cat6
CERTIFICATIONS	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Certifications	RoHS-Compliant
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>