



Cat6 Gigabit Snagless Slim UTP Ethernet Cable (RJ45 M/M), Blue, 6 in.

MODEL NUMBER: N201-S6N-BL



Connects critical components, such as computers, network adapters, routers, servers, modems, hubs and switches, in Gigabit Ethernet networks. Slim design increases airflow in tight spaces.

Description

The N201-S6N-BL Cat6 Gigabit Snagless Slim UTP Patch Cable is recommended for connecting network components like printers, computers, copiers, routers, servers, modems and switches in high-density data centers. Designed for fast transmission and excellent signal quality, this six-inch blue cable ensures peak performance throughout your local area network (LAN).

Manufactured from 28 AWG copper wire, the four-pair stranded UTP N201-S6N-BL delivers speeds up to Cat6 Gigabit/1 Gbps. Protected by a PVC jacket, this cable is more than 38% smaller in diameter than standard Cat6 cable, which increases airflow in tight spaces and makes it easier to install around corners and through cable management panels.

The RJ45 connectors' snagless design protects the locking tabs from being damaged or broken off during installation. Corrosion-resistant gold-plated copper contacts provide maximum conductivity and minimize data loss. Integral strain relief gives the cable extra flexibility, reduces stress, and helps the cable and connectors move freely without cracking.

Features

Ideal Solution for Your Cat6 Gigabit Ethernet Networking Needs

- Recommended for connecting computers, network adapters, routers, servers, modems, hubs and switches in high-density data centers
- Designed for fast transmission and excellent signal quality
- Ensures peak performance throughout your LAN
- Delivers speeds up to Cat6 Gigabit/1 Gbps

Highlights

- Over 38% slimmer than standard Cat6 cables
- Easy to route through cable management panels
- Rated for Cat6 Gigabit/1 Gbps communications
- 28 AWG 4-pair stranded UTP with PVC jacket
- Snagless connectors prevent damaged tabs during installation

Package Includes

- N201-S6N-BL Cat6 Gigabit Snagless Slim UTP Patch Cable (M/M), 6 in.



Special Slim Design

- More than 38% smaller in diameter than standard Cat6 cable
- Increases airflow in tight spaces
- Better flexibility for installing around corners and through cable management panels

Snagless RJ45 Male Connectors

- snagless boots prevent locking tabs from damage during installation

Premium Construction for Superior Performance

- Manufactured from 28 AWG 4-pair stranded UTP
- Gold-plated copper contacts for maximum conductivity and minimum data loss
- Integral strain relief protects cable and connectors from stress and cracking
- Rugged PVC jacket stands up to long-term use

Specifications

OVERVIEW	
UPC Code	037332206534
INPUT	
Cable Length (ft.)	0.5
Cable Length (m)	0.2
Cable Length (in.)	6
Cable Length (cm)	15.2
PHYSICAL	
Cable Shielding	UTP
Color	Blue
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.01
Shipping Weight (lbs.)	0.03
Snagless Connector	Yes
Wire Gauge (AWG)	28
Wire Gauge (OD - mm ²)	28
Wire Type	Stranded
COMMUNICATIONS	



Network Speed	1Gbps
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
FEATURES & SPECIFICATIONS	
Technology	Cat6
STANDARDS & COMPLIANCE	
Certifications	RoHS Compliant
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://products/tripp-lite.com/product-certification-agencies>