



Cat6 RJ45 Modular Plug for Round Stranded UTP Conductor 4-Pair, 100 Pack

MODEL NUMBER: N230-100-STR



Clear RJ45 connector terminates Cat6 round stranded conductor cabling in data and voice applications.

Description

The N230-100-STR contains 100 unshielded RJ45 modular plugs for round stranded UTP conductor 4-pair Cat6 cable. Recommended for creating your own custom-length Cat6 cable runs, these clear connectors come in a shatterproof plastic jar that's easy to pack in your toolbox and carry to your next installation.

Ideal for data and voice applications, these reliable RJ45 connectors are designed to terminate round Cat6 cable, such as Tripp Lite's N220-Series patch cabling. Their 15-micron gold-plated contacts ensure reliable signal transmission throughout the cable run, and their staggered nose pattern reduces near-end crosstalk. They are compatible with most RJ45 crimping tools (with AMP an exception).

Features

RJ45 Cat6 Connectors for Creating a Custom-Length Cat6 Cable

- 100 Cat6 RJ45 modular plugs in an easy-to-pack jar
- Ideal for data and voice applications
- Designed for terminating Cat6 round stranded UTP conductor 4-pair cable, such as Tripp Lite N220-Series

15m Gold-Plated Contacts for Premium Data Transfer

- Reliable signal transmission ensured throughout cable run
- Reduces near-end crosstalk (NEXT) with staggered nose pattern
- Works with most RJ45 crimping tools (excluding AMP)

Specifications

Highlights

- 100 Cat6 RJ45 plugs in an easy-to-carry, easy-to-pack plastic jar
- Works with most RJ45 crimping tools (excluding AMP)
- Premium data transfer through 15m gold-plated contacts
- Reduces near-end crosstalk (NEXT) with staggered nose pattern
- For use with Cat6 round stranded UTP conductor 4-pair cable

Applications

- Creating custom-length cables with Cat6 cable ends for use in data and voice applications

Package Includes

- (100) Cat6 RJ45 Modular Plugs



OVERVIEW	
UPC Code	037332206077
PHYSICAL	
Shipping Dimensions (hwd / cm)	6.65 x 11.18 x 6.10
Shipping Dimensions (hwd / in.)	2.62 x 4.40 x 2.40
Shipping Weight (kg)	0.18
Shipping Weight (lbs.)	0.40
ENVIRONMENTAL	
Operating Temperature Range	-40 TO 158 F (-40 TO 70 C)
Storage Temperature Range	-40 TO 158 F (-40 TO 70 C)
Relative Humidity	10% TO 90% RH, NON-CONDENSING
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
FEATURES & SPECIFICATIONS	
Technology	Cat6
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

[https:// products/product-certification-agencies](https://products.product-certification-agencies)