

SFP+ 10Gbase-CU Passive Twinax Copper Cable, SFP-H10GB-CU7M Compatible, Black, 7M (23-ft.)

MODEL NUMBER: N280-07M-BK



Description

Tripp Lite's Small Form Factor Pluggable (SFP+) passive copper cables are a high performance connectivity solution supporting 10Gbps Ethernet and Fibre Channel applications. Constructed with 24AWG to 30AWG (depending on length), 100ohm Twinaxial cable, Tripp Lite cables exceed the specs on most OEM cables, at a fraction of the cost. SFP+ cables were developed as cost effective, low power alternatives to fiber optic cables, in high speed interconnect applications, such as network storage and enterprise networking.

See "Features" tab for additional compatibility information

Features

- 7 m. (23 ft.) Black 24Awg SFP+ High Speed Passive Copper 10Gbps Cable
- Fully compliant to MSA SFF-8431 specification
- Equivalent to Cisco SFP-H10GB-CU7M (See the Support tab on this web page for additional cross references)
- Use in 10Gbps Ethernet and Fibre Channel applications
- 100ohm Twinaxial cable, Diecast metal shells, pull-to-release latching
- Support for 1x, 2x, 4x and 8x Fiber Channel data rates
- Hot-Pluggable SFP 20PIN footprint
- Low power consumption

Highlights

- 7 m. (23 ft.) Black 24AWG SFP+ High Speed Passive Copper 10Gbps Cable
- Fully compliant to MSA SFF-8431 specification
- Equivalent to Cisco SFP-H10GB-CU7M
- Low Cost alternative to Fiber Optic

System Requirements

Tripp Lite SFP+ Direct Attach Cable (DAC) Twinaxial cables conform to SFF-8431 standards, and as such can be used with the following manufacturers equipment that are open to 3rd party cables:

QLOGIC * EMULEX * JUNIPER * ARISTA * IBM * DELL * EXTREME EMC * BROADCOM * FINISAR * VOLTAIRE * CISCO

CONFIRMED EQUIPMENT LIST (

*ensure the latest firmware and software is installed)

CISCO NEXUS *

CISCO CATALYST *

CISCO CATALYST 3750x

CISCO CATALYST 2960

CISCO CATALYST 3500

CISCO CATALYST 3550

CISCO NEXUS 5010

ARISTA 70505-64

QUANTA T3048

EXTREME X250E

JUNIPER EX3200

NOT COMPATIBLE TO 3RD

PARTY CABLES: HP and

BROCADE



Package Includes

- 7 m. (23 ft.) Black 24Awg SFP+ High Speed Passive Copper 10Gbps Cable

Specifications

OVERVIEW	
UPC Code	037332178206
INPUT	
Cable Length (ft.)	23
Cable Length (m)	7
PHYSICAL	
Wire Gauge (AWG)	24
Shipping Dimensions (hwd / in.)	17.000 x 14.000 x 0.500
Shipping Dimensions (hwd / cm)	43.18 x 35.56 x 1.27
Shipping Weight (lbs.)	0.9500
Shipping Weight (kg)	0.43
Color	Black
CONNECTIONS	
Side A - Connector 1	SFP+ (MALE)
Side B - Connector 1	SFP+ (MALE)
FEATURES & SPECIFICATIONS	
Technology	SFP+/QSPP+/QSFP28
CERTIFICATIONS	
Certifications	RoHS compliant
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>