


## Duplex Singlemode 8.3/125 Fiber Patch Cable (LC to SC/APC), 2M (6-ft.)

MODEL NUMBER: N366-02M-AP



### Description

Tripp Lite's 2-meter, single mode duplex fiber optic LC to SC/APC patch cable is manufactured from 8.3/125 zipcord fiber. The cable has SC Angle Physical Polish connectors on one end, LC connectors on the other, a PVC jacket, and is FDDI and OFNR rated. Duplex single mode fiber is most commonly used in LAN applications. The Angled connector face prevents light entering the fiber to bounce back into the laser, destabilizing it. Check your fiber transceivers user manual to see if an APC cable is warranted.

### Features

- LC to SC/APC (Angle Physical Contact), 2 Meter Fiber Patch cable
- Manufactured from 8.3/125 duplex (zipcord) fiber
- PVC jacket
- Length: 1-meter. Connectors: 2 SC (Green ) and 2 LC connectors on each end
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)
- Fiber optic distributed data interface (FDDI) rated
- OFNR (riser rated)

## Specifications

OVERVIEW	
UPC Code	037332150967
Clad Diameter	125
Core Diameter	8.3

### Highlights

- LC to SC/APC (Angle Physical Contact), 2 Meter Fiber Patch cable
- Premium PVC 8.3/125 micron singlemode patch cables
- Attenuation loss meets or exceeds the latest industry standards
- Twice the bandwidth throughput of multimode cable

### Package Includes

- 2 Meter (6-ft.) Duplex SMF 8.3/125 Patch Cable, LC to SC/APC



Number of Fibers	2
Optical Mode	OS2
<b>INPUT</b>	
Cable Length (ft.)	6.6
Cable Length (m)	2
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	9.000 x 7.000 x 0.500
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.0600
Shipping Weight (kg)	0.03
Color	Yellow
<b>CONNECTIONS</b>	
Side A - Connector 1	LC DUPLEX (MALE)
Side B - Connector 1	SC DUPLEX (MALE)
<b>FEATURES &amp; SPECIFICATIONS</b>	
Technology	Singlemode
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.triplite.com/products/product-certification-agencies>