




# High-Density Copper/Fiber Enclosure Mini Panel, 1U, 4-Cassette Capacity

MODEL NUMBER: N484-01U-MINI



1U rack-mount enclosure panel allows you to add up to 4 high-density copper or fiber cassettes to your rack installation.

## Features

**1U Copper/Fiber Enclosure Adds Up to 4 High-Density Cassettes to Your Rack Installation** Insert up to four Tripp Lite N484-Series copper and/or fiber cassettes (sold separately) into this cost-effective enclosure panel. Mounting in just 1U of space in an EIA-standard 19-inch rack, the compact N484-01U-MINI includes no protruding front door or rear cable management, which allows more inside rack space. It is ideal for a wide range of singlemode and multimode applications in small and medium enterprise environments where equipment is connected in up to three adjacent racks. The fully passive mini panel adds no heat or cooling load.

**Easily Accommodates a Variety of Cassette Types** The heavy-duty steel N484-01U-MINI houses as many as four N484-Series cassettes, including RJ45 and SFP+ copper and LC duplex and MTP/MPO fiber, and 48 ports within its 1U chassis. In the case of fiber cassettes, the panel lets you interconnect any combination of 10 Gb, 40 Gb and 100/120 Gb network equipment in a simple, elegant and highly flexible way. It seamlessly connects to your existing cabling infrastructure and supports a wide range of applications and protocols in high-density telecom and data center environments.

## Highlights

- 1U chassis accepts fiber and copper cassettes, including RJ45, SFP+, LC and MTP/MPO
- Allows interconnection of any combination of 10 Gb, 40 Gb and 100/120 Gb fiber equipment
- Compact design eliminates front door and rear cable bar to allow more inside rack space
- Fully passive mini enclosure panel adds no heat or cooling load
- Ideal for single- and multimode applications in small/medium enterprise environments

## Applications

Connect, organize and manage copper and fiber optic cable connections in your high-density telecom or data center environment

## System Requirements

- Compatible with Tripp Lite N484-Series copper and fiber cassettes

## Package Includes

- N484-01U-MINI High-Density Copper/Fiber Enclosure Mini Panel
- Quick Start Guide

## Specifications

OVERVIEW	
UPC Code	037332250438
PHYSICAL	



Cassette Capacity	4
Cassette Type	Panel Enclosure; Pass-through
Color	Black
Material of Construction	Aluminum, Steel
Primary Form Factor	Rackmount
Rack Height	1U
Rackmountable	Yes
Unit Dimensions (hwd / in.)	1.73 x 18.98 x 1.19
Unit Weight (kg)	0.62
Unit Weight (lbs.)	1.37
<b>FEATURES &amp; SPECIFICATIONS</b>	
Technology	Cat5/5e; Cat6; Cat6a; Multimode; MTP/MPO
<b>SPECIAL FEATURES</b>	
Keystone Jacks	No
All-in-One Kit	No
Down-Angled Ports	No
Built-in Cables	No
Offset Ports	No
Color-Coded Connections	No
Numbered Ports	No
EIA/TIA 2/32 Spacing	No
Labeled Ports	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Approvals	RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://products/tripp-lite.com/product-certification-agencies>