




Hospital-Grade Extension Cord, NEMA 5-15P to NEMA 5-15R - Green Dot, 15A, 125V, 14 AWG, 6 ft., Gray

MODEL NUMBER: P024-006-GY-HG



Hospital-grade extension cord connects two devices with 5-15P-HG/5-15R-HG power connectors in a hospital or other medical facility.

Features

Heavy-Duty Hospital-Grade Extension Cord is a Safe Solution for Medical Facilities This hospital-grade power cord is designed for computers, mobile carts, printers, scanners, monitors and other compatible hospital equipment within a healthcare facility and outside patient-care vicinities. It features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. The six-foot length allows you flexibility in placing equipment with respect to the power outlet.

Designed and Tested to Strict Hospital-Grade Standards This cord is tested to ANSI/UL 62 and 817 standards, as well as CAN/CSA C22.2 no. 21 and 49 standards, ensuring it's a dependable power solution for hospital environments.

Color-Coded to Avoid Misidentification That Can Cause Costly Downtime This extension cord features a gray SJT jacket and fully molded gray ends. The color-coding allows easy, fast identification in a crowded surge protector and helps prevent the cable from becoming inadvertently disconnected.

Highlights

- Recommended for connecting devices to power outlets outside patient-care vicinities
- 6 ft. length allows flexibility in placing devices in relationship to AC outlet
- 6-foot extension cord replaces or upgrades power cord provided by manufacturer
- 5-15P-HG plug connects to AC power; 5-15R-HG end connects to device's input cord
- Color-coded gray for fast, easy identification in a crowded PDU, UPS or surge protector

Applications

- Connect devices like PCs, mobile carts, monitors and printers to a power outlet up to 6 ft. away in a hospital environment outside patient-care vicinities
- Extend an existing power connection up to 6 ft. to more easily place a device or reach a power source
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

- P024-006-GY-HG Hospital-Grade Extension Cord, 5-15P-HG to 5-15R-HG, 6 ft., Gray

Specifications



OVERVIEW	
UPC Code	037332200136
Country/Region	North America
INPUT	
Maximum Input Amps	15
Cable Length (ft.)	6
Cable Length (m)	1.8
Voltage Compatibility (VAC)	125
PHYSICAL	
Color	Gray
Number of Conductors	3
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	35.05 x 27.69 x 1.27
Shipping Dimensions (hwd / in.)	13.80 x 10.90 x 0.50
Shipping Weight (kg)	0.36
Shipping Weight (lbs.)	0.80
Wire Gauge (AWG)	14
Wire Gauge (OD - mm ²)	2.08
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P-HG
Side B - Connector 1	NEMA 5-15R
SPECIAL FEATURES	
High Voltage	No
Locking Plug	No
STANDARDS & COMPLIANCE	
Certifications	ANSI/UL 62 AND 817, CAN/CSA C22.2 NO. 21 AND 42, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:



[https:// products/product-certification-agencies](https://products/product-certification-agencies)