



## Desktop Computer Power Cord, NEMA 5-15P to C13, 5-Pack - 10A, 125V, 18 AWG, 2 ft., Black

MODEL NUMBER: P030-002-5



Computer power cables connect your server, switch, router and other devices to a surge protector, PDU or UPS system with 5-15R outlets.

### Features

**Desktop Computer Power Cords Connect Essential Network Equipment** This computer power supply cable is designed for keeping mission-critical network equipment operating at all times. You can use it to connect a computer, monitor, printer, server, switch, router or other device with a C14 power inlet to an AC wall outlet, surge protector, UPS system or PDU. The two-foot length helps reduce cable clutter and minimize the risk of tripping. Five power supply cables are included.

### Highlights

- Recommended for powering servers, switches, routers and other network devices
- 2 ft. length allows flexibility in placing devices, while avoiding cable clutter
- Ideal replacements for worn-out or missing NEMA 5-15P to C13 power cables

### Applications

- Connect devices like servers, switches and routers to a PDU in your data center
- Extend existing power connections up to 2 ft. to more easily place devices or reach a power source
- Provide high-quality replacements for worn-out or missing power cords

### Package Includes

- P030-002-5 Desktop Computer Power Cord, NEMA 5-15P to C13, 5-Pack, 2 ft., Black

## Specifications

OVERVIEW	
UPC Code	037332143280
Country/Region	North America
INPUT	
Maximum Input Amps	10
Cable Length (ft.)	2
Cable Length (m)	0.6



Voltage Compatibility (VAC)	125
<b>PHYSICAL</b>	
Color	Black
Number of Conductors	3
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	25.35 x 18.01 x 1.27
Shipping Dimensions (hwd / in.)	9.98 x 7.09 x 0.50
Shipping Weight (kg)	0.50
Shipping Weight (lbs.)	1.10
Wire Gauge (AWG)	18
Wire Gauge (OD - mm <sup>2</sup> )	0.82
<b>CONNECTIONS</b>	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	IEC-320-C13
<b>SPECIAL FEATURES</b>	
High Voltage	No
Locking Plug	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://products/product-certification-agencies>