



# Computer Power Cord, C19 to NEMA 5-15P - Heavy Duty, 15A, 125V, 14 AWG, 10 ft., Black

MODEL NUMBER: P034-010



C19 to 5-15P adapter connects devices with C20/NEMA 5-15R power connectors or extends your existing power connection by 10 ft.

### Features

**Heavy-Duty Computer Power Cable for Devices That Require a Heavy-Gauge Connection** This C19 to 5-15P computer power cord features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. It can be used to connect a computer, server, monitor or drive to a UPS system or PDU or replace or upgrade the standard power cord provided by the device's manufacturer. The 10-foot length allows you great flexibility in placing equipment with respect to the power outlet.

### Highlights

- Recommended for powering computers, servers and other network devices
- 10 ft. length allows great flexibility in placing devices in relationship to AC outlet
- Heavy-duty computer power cord replaces or upgrades cord provided by manufacturer
- Thick 14 AWG wire gauge manages high power levels required for larger equipment

### Applications

- Connect devices like computers, servers and monitors to a PDU up to 10 ft. away in your data center
- Extend an existing power connection up to 10 ft. to more easily place a device or reach a power source
- Update or replace the standard power cord provided by a device's original manufacturer

### Package Includes

- P034-010 Computer Power Cable, C19 to 5-15P, 10 ft., Black

## Specifications

OVERVIEW	
UPC Code	037332140920
Country/Region	North America



<b>INPUT</b>	
Maximum Input Amps	15
Cable Length (ft.)	10
Cable Length (m)	3.1
Voltage Compatibility (VAC)	125
<b>PHYSICAL</b>	
Color	Black
Number of Conductors	3
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	32.51 x 22.61 x 1.27
Shipping Dimensions (hwd / in.)	12.80 x 8.90 x 0.50
Shipping Weight (kg)	0.50
Shipping Weight (lbs.)	1.10
Wire Gauge (AWG)	14
Wire Gauge (OD - mm <sup>2</sup> )	2.08
<b>CONNECTIONS</b>	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	IEC-320-C19
<b>SPECIAL FEATURES</b>	
High Voltage	No
Locking Plug	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

[https:// products/product-certification-agencies](https://products/product-certification-agencies)