



Power Cord, C19 to NEMA 5-20P - Heavy Duty, 20A, 125V, 12 AWG, 10 ft., Black

MODEL NUMBER: P049-010



Heavy-duty extension cord transforms a C20 plug into a NEMA 5-20P plug and extends an existing connection up to 10 ft.

Features

Heavy-Duty Extension Cable Connects Devices That Require a Heavy-Gauge Connection This heavy-duty extension cord features 12 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. This C19 to 5-20P cord can be used to connect a high-output device to a wall outlet or a PDU or UPS with 5-20R outlets. It is also a recommended replacement or upgrade of a standard power cord provided by the device's manufacturer. The 10-foot length allows you great flexibility in placing equipment with respect to the power outlet.

Highlights

- 10 ft. length allows great flexibility in placing devices in relationship to AC outlet
- Heavy-duty cable replaces or upgrades standard power cord provided by manufacturer
- Thick 12 AWG wire gauge manages high power levels required for larger equipment

Applications

- Connect devices to a power outlet up to 10 ft. away in your office or work space
- Transform a C20 plug into a NEMA 5-20P plug with no electrician needed
- Extend an existing power connection up to 10 ft. to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

- P049-010 C19 to 5-20P Heavy-Duty Extension Cord, 10 ft., Black

Specifications

OVERVIEW	
UPC Code	037332140944
Country/Region	North America
INPUT	



Maximum Input Amps	20
Cable Length (ft.)	10
Cable Length (m)	3.1
Voltage Compatibility (VAC)	125
PHYSICAL	
Color	Black
Number of Conductors	3
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	32.51 x 22.61 x 0.25
Shipping Dimensions (hwd / in.)	12.80 x 8.90 x 0.10
Shipping Weight (kg)	0.77
Shipping Weight (lbs.)	1.70
Wire Gauge (AWG)	12
Wire Gauge (OD - mm ²)	3.31
CONNECTIONS	
Side A - Connector 1	NEMA 5-20P
Side B - Connector 1	IEC-320-C19
SPECIAL FEATURES	
High Voltage	No
Locking Plug	No
STANDARDS & COMPLIANCE	
Approvals	UL-approved
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

[https:// products/product-certification-agencies](https://products.product-certification-agencies)