



## Premium High-Speed HDMI Cable with Ethernet and Gripping Connectors, UHD 4K @ 60 Hz (M/M), 3 ft.

MODEL NUMBER: P569-003-CERT



HDMI-certified cable with high-grip connectors transmits digital audio/video and Ethernet signals to a 4K-enabled television, projector or monitor. Ideal for all multimedia applications that display UHD video.

### Description

The P569-003-CERT Premium High-Speed HDMI Cable with Ethernet (M/M) is recommended for home theater systems and other applications that display Ultra High Definition (UHD) video and multi-channel audio. It connects an HDMI-enabled source device, such as a Blu-ray™ player, video game system or computer, to a 4K-enabled television, monitor or projector.

This three-foot cable is specially certified by HDMI to guarantee UHD video resolutions up to 4096 x 2160 (4K x 2K), including 1080p, at 60 Hz, as specified in HDMI 2.0. Burgundy molding signifies the cable's status as an HDMI Premium Certified Cable. Distinctive high-grip male connectors ensure a secure, tight fit to prevent the cable from coming loose accidentally.

The P569-003-CERT also supports data transfer speeds up to 18 Gbps and 3D video. Backward compatible with previous HDMI generations, the P569-003-CERT works in all HDMI cabling scenarios.

This latest generation HDMI cable supports Ethernet data connectivity, which allows web-capable devices to share their internet connection with other connected devices. An audio return channel simplifies setups between displays and A/V receivers. When used with an Apple® digital A/V adapter, it supports iPad2® video mirroring for playing games, watching videos or displaying presentations.

The 28 AWG cable features premium foil and braid shielding to deliver top-of-the-line signal quality and protection from EMI/RFI interference. Gold-plated connectors and contacts ensure excellent conductivity.

### Features

**Connects HDMI Source to 4K TV, Projector or Monitor** Recommended for home theater systems, classrooms, conference rooms, data centers, digital signage and other applications that display UHD video and multi-channel audio

**Premium Certified by HDMI** Certified to guarantee UHD video resolutions up to 4K @ 60 Hz (4096 x 2160), as specified in HDMI 2.0 Special burgundy molding signifies Premium Certified status

**Distinctive High-Grip Connectors** Male plugs specifically designed for secure, tight fit that prevents accidental disconnection

**High Performance and Wide Compatibility** Supports data transfer speeds up to 18 Gbps and 3D Audio return channel simplifies setup between display and receiver Supports iPad2 video mirroring when used with Apple digital A/V adapter Backward compatible with previous HDMI generations Works in all HDMI

### Highlights

- Supports UHD video resolutions up to 4096 x 2160 (4K x 2K), as specified in HDMI 2.0
- Supports data transfer speeds up to 18 Gbps
- Ideal for connecting 4K televisions
- Tested for highest performance and ultra reliability
- Special high-grip plugs prevent accidental disconnections

### System Requirements

- Video source with HDMI output
- Display with HDMI input

### Package Includes

- P569-003-CERT Premium High-Speed HDMI Cable with Ethernet (M/M), 3 ft.



cabling scenarios

**Superior Construction Ensures a Flawless Signal** Fully molded 28 AWG construction with integral strain relief for durability and long life Premium foil and braid shielding for EMI/RFI noise protection Corrosion-resistant gold-plated connectors and contacts for optimal signal transfer Flexible PVC jacket easy to install in tight spaces

## Specifications

OVERVIEW	
UPC Code	037332198600
INPUT	
Cable Length (ft.)	3
Cable Length (m)	0.9
Cable Length (in.)	36
Cable Length (cm)	91.44
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	1.27 x 23.37 x 17.53
Shipping Dimensions (hwd / in.)	0.50 x 9.20 x 6.90
Shipping Weight (kg)	0.05
Shipping Weight (lbs.)	0.10
CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	HDMI (MALE)
FEATURES & SPECIFICATIONS	
Technology	HDMI
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://products.com/product-certification-agencies>