



# High Speed HDMI Cable with Ethernet, UHD 4K, Digital Video with Audio, In-Wall CL2-Rated (M/M), 10 ft.

MODEL NUMBER: P569-010-CL2



### Description

Tripp Lite In-Wall CL2-Rated HDMI cables are the latest generation of Digital Video and Audio: High Speed HDMI with Ethernet. These cables offer the highest level of performance by HDMI: supports Ethernet Data Connectivity, Audio Return Channel, 3D support, and Ultra High Definition (UHD) 4Kx2K video resolutions up to 3840 x 2160. High Speed (or "category 2") HDMI cables have been tested to perform at speeds of 340Mhz or up to 18 Gbps, which is the highest bandwidth currently available over an HDMI cable. These cables are backward compatible with previous versions of HDMI, and will work in all HDMI cabling scenarios.

### Features

- 10-ft. High Speed HDMI Cable with Ethernet (v1.4)
- In-wall, CL2-rated jacket
- Supports Ultra High Definition (UHD) 4Kx2K video resolutions up to 3840 x 2160
- Supports transmission speeds up to 18 Gbps
- Backward compatible to previous HDMI generations
- Fully molded cables, with Gold plated connectors assures long life

## Specifications

OVERVIEW	
UPC Code	037332188243
INPUT	

### Highlights

- 10-ft. High Speed HDMI Cable with Ethernet (v1.4)
- In-wall, CL2-rated jacket
- Supports Ultra High Definition (UHD) 4Kx2K video resolutions up to 3840 x 2160
- Supports transmission speeds up to 18 Gbps
- Backward compatible to previous HDMI generations

### System Requirements

- HDMI video source and HDMI enabled TV / Monitor

### Package Includes

- 10-ft. High Speed HDMI Cable with Ethernet (v1.4), In-Wall CL2-Rated



Cable Length (ft.)	10
Cable Length (m)	3.1
<b>PHYSICAL</b>	
Color	Black
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.15
Shipping Weight (lbs.)	0.34
<b>CONNECTIONS</b>	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	HDMI (MALE)
<b>FEATURES &amp; SPECIFICATIONS</b>	
Technology	HDMI
<b>SPECIAL FEATURES</b>	
Fire Rating	CL2 Rated
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

[https://  
products/product-certification-agencies](https://products.product-certification-agencies)