



DisplayPort 1.2 to DVI Active Adapter Cable, DP with Latches to DVI (M/M), 6 ft.

MODEL NUMBER: **P581-006-V2**

Converts a DisplayPort v1.2 video signal for display on a DVI monitor, projector or television.

Description

The P581-006-V2 DisplayPort 1.2 to DVI Active Adapter Cable connects a DisplayPort computer to the DVI port on a monitor, projector or television. With a latching DisplayPort male connector on one end and a DVI-D male connector on the other, this cable requires no separate adapter. It lets you use your existing DVI display instead of buying a new DisplayPort monitor.

Ideal for displaying video on a large monitor or digital sign, this cable supports computer video resolutions up to 1920 x 1200 and high-definition video resolutions up to 1920 x 1080 (1080p). It converts both Single-Mode and Dual-Mode (DP++) DisplayPort output, and is perfect for use with graphics cards, such as AMD Eyefinity, that do not output DP++ signals.

First-class foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI interference. Gold-plated connectors and contacts ensure excellent conductivity. The Displayport plug latches to the port to provide a secure connection. Integral strain relief ensures the cable and molded connectors last a long time.

Features

Send High-Quality DisplayPort v1.2 Video Signals to a DVI Display

- Connects DisplayPort computer to DVI-enabled monitor, projector or TV
- Ideal for displaying video on large monitor or digital sign
- DVI-D and DisplayPort male connectors
- No separate adapter required

Vibrant, Superior Video Quality

- Supports computer video resolutions up to 1920 x 1200
- Supports HD video resolutions up to 1920 x 1080 (1080p)
- Converts Single-Mode and Dual-Mode (DP++) DisplayPort output
- Perfect for use with graphics cards, such as AMD Eyefinity, that do not output DP++ signals

Superior Materials for Superior Performance

- Double shielding with foil and braid for maximum EMI/RFI protection
- Gold-plated connectors and contacts for excellent conductivity
- Latching Displayport plug for secure connection
- Integral strain relief for long life

Specifications

Highlights

- Active adapter cable for use with any Displayport port
- Supports computer video resolutions up to 1920 x 1200
- Supports HD video resolutions up to 1920 x 1080 (1080p)
- No separate adapter required
- Gold-plated connectors and contacts

Package Includes

- P581-006-V2 DisplayPort 1.2 to DVI Active Adapter Cable, 6 ft.



OVERVIEW	
UPC Code	037332191977
INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.8
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.18
Shipping Weight (lbs.)	0.40
ENVIRONMENTAL	
Operating Temperature Range	32~113°F (0~45°C)
Storage Temperature Range	14~158°F (-10~70°C)
Operating Humidity Range	10%~85% RH, Non-Condensing
Storage Humidity Range	5%~90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	DVI-D DUAL-LINK (MALE) (WIRED TO DVI-D SINGLE-LINK)
FEATURES & SPECIFICATIONS	
Max Supported Video Resolution	1920 x 1200 @60Hz
Displayport Specification	1.2
Max Supported Color Depth	24-bit True Color
Technology	DVI; DisplayPort
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://products/product-certification-agencies>