

Plug-Lock Inserts (C14 power cord to C13 outlet), Black, 100 pack

MODEL NUMBER: PLC13BK



Description

Tripp Lite PLC13BK BLACK color Plug-lock inserts prevent accidental disconnection of C14 plug-in power cords from C13 output receptacles. IEC 60320 plug-in electrical cords are frequently loose-fitting and are often subject to accidental disconnection during routine network maintenance. To prevent critical equipment plugs from getting knocked loose, place a Plug-lock insert over any C14 input cord and connect it to any C13 outlet. The insert strengthens the connection of the plug to the outlet, keeping critical equipment plugged-in and running during routine rack access and maintenance. Plug-lock inserts provide a no-clutter alternative to common zip-tie cord retention schemes and a low cost answer to expensive proprietary locking plug and outlet hardware. PLC13BK Plug-lock inserts ship in packages of 100.

Features

- Tripp Lite PLC13BK Plug-lock inserts prevent accidental disconnection of C14 plug-in power cords from C13 outlets
- BLACK color PLC13BK inserts ship in packages of 100 pieces
- Corrects loose-fitting IEC60320 power connections that could lead to accidental disconnection of power cables
- Plug-lock inserts strengthen the connection of your C14 plug-in device to any C13 outlet, keeping vital network equipment plugged in and running during routine rack access and maintenance
- Universal compatibility ensures proper fit and enhanced plug retention when used with any standard C14 plug and C13 outlet combination; no proprietary cables or outlets required
- Simple installation, just place a Plug-lock insert over any C14 equipment power cord and plug it in
- Pull tabs enable safe retraction of the insert from powered C13 outlets
- Plug-lock inserts provide a no-clutter alternative to common zip-tie cord retention schemes and prevents

Highlights

- PLC13BK Plug-lock inserts keep C14 power cords connected to C13 outlets
- Prevents accidental disconnection of network hardware during routine rack maintenance
- Universal compatibility, no special cables, outlets or special PDU hardware required
- BLACK color inserts ship in packages of 100, more colors available

Package Includes

- 100 BLACK color C14 plug / C13 outlet compatible Plug-lock inserts



reliance on lesser elegant remedies involving duct tape, electrical tape or super glue

- High strength PA66 nylon UL94 material with V2 flame rating

Specifications

OVERVIEW	
UPC Code	037332179678
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	9.02 x 32.51 x 21.79
Shipping Dimensions (hwd / in.)	3.55 x 12.80 x 8.58
Shipping Weight (kg)	0.39
Shipping Weight (lbs.)	0.87
Unit Dimensions (hwd / cm)	3.18 x 3.05 x 2.29
Unit Dimensions (hwd / in.)	1.25 x 1.2 x .9
STANDARDS & COMPLIANCE	
Approvals	TAA Compliant
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://products.com/product-certification-agencies>