



Power It! 6-Outlet Power Strip, 6 ft. Cord, Black Housing

MODEL NUMBER: **PS66B**



Highlights

- 6 NEMA 5-15R outlets
- 15A resettable circuit breaker prevents dangerous overloads
- Lighted on/off switch gives one-touch control over components
- 6 ft. AC power cord with NEMA 5-15P plug
- Bottom keyhole slots for mounting to wall or desk

Package Includes

- PS66B Power It! 6-Outlet Power Strip, Black Housing
- Owner's manual

Connect up to 6 electrical devices to a single AC wall socket. Ideal for connecting appliances, power tools, lighting and other electrical equipment in your home, office or work site.

Description

The PS66B Power It!™ 6-Outlet Power Strip is a reliable, compact, cost-effective 120V 1875W power strip that lets you connect up to six electrical devices to a single AC wall socket. With a six-foot AC power cord with NEMA 5-15P plug, this multi-outlet power strip is ideal for use with appliances, power tools, lighting and other electrical equipment in homes, offices and work sites.

Your components plug into six NEMA 5-15R outlets compatible with all standard electrical equipment. Integrated 15-amp circuit breaker protects all outlets against dangerous overloads. Lighted on/off switch provides one-touch control over connected equipment. Keyhole slots incorporated into the bottom panel provide convenient wall or desk mounting options for the black plastic housing.

Features

6 Outlets Power All Standard Electronics

- 6 NEMA 5-15R AC outlets accept most appliances, power tools, lights and other devices

Premium Safety Features

- Lighted on/off switch provides one-touch control over connected equipment
- Integrated 15A circuit breaker protects outlets against overloads
- UL and cUL approved

Fits Effortlessly Into Your Home, Office or Work Site

- 6 ft. AC power cord with NEMA 5-15P plug
- Keyhole slots on bottom panel provide convenient wall or desk mounting options



- Black plastic housing designed for long life

Specifications

OVERVIEW	
UPC Code	037332190765
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output (Watts)	1875
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Overload Protection	15A circuit breaker
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 6
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	Illuminated on/off switch controls power to all outlets
PHYSICAL	
Antimicrobial Coating	No
Color	Black
Color (AC Line Cord)	Black
Integrated Keyhole Mounting Slots	Yes
Material of Construction	Plastic



Receptacle Color	Black
Shipping Dimensions (hwd / cm)	28.02 x 10.59 x 3.99
Shipping Dimensions (hwd / in.)	11.03 x 4.17 x 1.57
Shipping Weight (kg)	0.48
Shipping Weight (lbs.)	1.05
Unit Dimensions (hwd / cm)	23.3 x 3.81 x 3.81
Unit Dimensions (hwd / in.)	9.5 x 1.5 x 1.5
Unit Weight (kg)	0.37
Unit Weight (lbs.)	.81
STANDARDS & COMPLIANCE	
Canada	cUL
Additional International Approvals	Complies with RoHS (Restriction of Hazardous Substances Directive)
UL1363 (Power Tap)	UL1363
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: [https:// products/product-certification-agencies](https://products.product-certification-agencies)