



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: SUPER6OMNID

### Protect It! Surge Suppressor



#### Highlights

- 6 universal outlets
- 1.8 m power cord with German/French plug
- 750 joule rating
- Lighted on/off switch with integrated circuit breaker

#### Description

Tripp Lite's Protect It!™ SUPER6OMNI D offers economical AC surge suppression for full protection of 220-250V workstations, desktop PCs, telecom systems and other sensitive electronics. Built-in AC surge suppression shields connected equipment from damage and performance problems due to transient surges. The SUPER6OMNI D offers 6 universal outlets and a 1.8 meter AC line cord with German/French plug. AC suppression rated at 750 joules shields equipment from surges and line noise. Lighted on/off switch with integrated circuit breaker provides power control over connected equipment. Right-angle outlets keep connected cords from blocking adjacent outlets. Attractive light gray high-impact housing.

INPUT: 1.8 m AC line cord with German/French plug

OUTPUT: 6 universal receptacles

ELECTRICAL: 220-250V AC, 50/60Hz, 10A

FORMAT: Corded multi-outlet strip

SUPPRESSION: - AC: 750 joules

#### Applications

- Ideal for any desktop, network or home computing application requiring AC surge suppression

#### Package Includes

- SUPER6OMNI D AC surge suppressor
- Instruction manual and warranty information

#### Features

- Protect It!™ SUPER6OMNI D offers economical AC surge suppression
- 750 joules AC surge suppression shields equipment from surges and line noise
- 6 universal outlets protect computers and peripherals
- 1.8 m AC line cord with German/French plug
- Built-in power switch and 10 amp circuit breaker offers power control and overload protection over all outlets

- Fail-safe thermal fusing protects against fire and other damage in the event of an extreme, extended overvoltage or surge condition
- Attractive light gray high-impact housing with keyhole mounting tabs allow versatile placement options
- Right-angle outlets keep connected cords from blocking adjacent outlets

## Specifications

<b>OVERVIEW</b>	
Intended Application	Home/Office
<b>OUTPUT</b>	
Frequency compatibility	50 / 60 Hz
Circuit Breaker (amps)	10
Overload protection	10A resettable illuminated combo switch/circuit breaker
Outlet quantity / type	6 universal outlets
Outlet orientation	right-angled
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	230V AC
Recommended Electrical Service	230V (220-250V)
Input connection type	German
Input cord length (ft.)	6
Input cord length (m)	1.8
Voltage compatibility (VAC)	220-250
Maximum Surge Amps	13500
<b>LEDS ALARMS &amp; SWITCHES</b>	
Switches	Two position power switch
<b>SURGE / NOISE SUPPRESSION</b>	
AC suppression joule rating	750
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
<b>PHYSICAL</b>	
Shipping weight (lbs)	1.32
Shipping weight (kg)	0.60
Unit Dimensions (HWD/in)	15.50 x 2.50 x 1.25
Unit Dimensions (HWD/cm)	39.4 x 6.4 x 3.2

<b>Shipping Dimensions (HWD/in)</b>	18.50 x 4.50 x 2.00
<b>Shipping Dimensions (HWD/cm)</b>	47.0 x 11.4 x 5.1
<b>Unit weight (lbs)</b>	1.0
<b>Unit weight (kg)</b>	0.45
<b>Material of construction</b>	Plastic
<b>Integrated keyhole mounting tabs</b>	Yes - slotted
<b>AC line cord color</b>	light gray
<b>Style</b>	Strip
<b>Outlets center to center measurement</b>	51mm
<b>Keyhole slot center to center measurement</b>	219.5mm
<b>WARRANTY</b>	
<b>Product Warranty Period (Worldwide)</b>	Lifetime limited warranty

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=2733](http://www.tripplite.com/en/products/model.cfm?txtModelID=2733).

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.