



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: SUPER7TEL15

### 7-outlet, 15-ft cord, 2520 joule, Modem/fax protection, Protect It! Surge Suppressor



#### Highlights

- 7 outlets / 15-ft. cord
- 2520 joule rating
- Modem/fax surge protection
- \$75,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico & Canada only)

#### Description

Tripp Lite's SUPER7TEL15 surge suppressor offers complete AC and phone line surge suppression for comprehensive protection of workstations, desktop PCs, telecom systems and other sensitive electronics. Heavy grade AC surge suppression shields connected equipment from damage and performance problems due to transient surges. Set of RJ11 telephone line suppression jacks protect dialup and DSL modem lines, fax machines, cordless phones and more. SUPER7TEL15 offers 7 total outlets, extra-long 15 foot cord with space-saving angled plug and diagnostic LEDs to warn of wiring problems and suppressor damage. Heavy grade AC suppression rated at 2520 joules shields equipment from surges and line noise. Attractive gray suppressor housing with keyhole mounting slots and 3 designated transformer plug outlets offers convenient protection of desktop computer equipment and accessories. \$75,000 [connected equipment insurance](#) (USA, Puerto Rico and Canada only). PLUG/OUTLETS: Input: NEMA5-15P/Output: 7 NEMA5-15R/15-ft. AC line cord ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle) FORMAT: Corded multi-outlet strip with 3 transformer spaced outlets SUPPRESSION: AC: 150V RMS Clamping/2520 joules/330 L-G, 400 L-N, 400 N-G UL1449 Let-through Phone: Single telephone line surge suppression (RJ11 jacks, 2 wire, 1 line)

#### Applications

- Ideal for any desktop, network or home computing application requiring AC and dialup or DSL modem line protection

#### Package Includes

- SUPER7TEL15 Surge Suppressor
- 6-ft. telephone cord
- Instruction manual with warranty information

#### Features

- 2520 joules AC surge suppression shields equipment from the strongest surges and line noise
- 7 AC outlets with room for 3 transformer plugs without blocking outlets covers computers and all peripherals
- Phone line surge suppression protects both dialup and DSL modems, plus fax machines, cordless phones and more (pair of RJ11 jacks, 2 wire, 1 line, includes 6 ft phone cable)
- Extra long 15 foot AC line cable with space-saving angle input plug conveniently reaches distant outlets
- Built-in power switch and 15 amp circuit breaker offers power control and overload protection over all outlets
- Fail-safe thermal fusing protects against fire and other damage in the event of an extreme, extended overvoltage or surge condition
- Diagnostic LEDs confirm outlet grounding and surge suppression status
- Attractive gray suppressor housing with keyhole mounting tabs allow versatile placement options
- UL1449 Rated, UL1363 (Power Tap), UL497A (Communications), Meets FCC part 68 rules, cUL (Canada)
- Exceeds IEEE 587 category A & B surge suppression specifications
- \$75,000 Ultimate Lifetime [connected equipment insurance](#) (USA and Canada Only)

#### Specifications

<b>OVERVIEW</b>	
Intended Application	Home/Office
<b>OUTPUT</b>	
Frequency compatibility	50 / 60 Hz
Output watts	1800
Circuit Breaker (amps)	15
Outlet quantity / type	7 NEMA 5-15R
Transformer accommodation	Supports 3 large transformer plug accessories without covering remaining outlets, accepts up to 5 transformers total
Outlet orientation	Single row of 5, plus 2 side mounted outlets
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P
Input plug features	Space-saving right angle input plug
Input cord length (ft.)	15
Input cord length (m)	4.57
Input cord gauge, type	14 gauge, SJT
Voltage compatibility (VAC)	120
Maximum Surge Amps	156000
<b>LEDS ALARMS &amp; SWITCHES</b>	
Switches	Two position on/off power switch
Diagnostic LEDs	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
<b>SURGE / NOISE SUPPRESSION</b>	
AC suppression joule rating	2520
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping voltage (RMS)	150
UL1449 let through rating	330 L-G, 400 L-N, 400 N-G
EMI / RFI filtering	Up to 20 dB
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No

<b>PHYSICAL</b>	
Shipping weight (lbs)	2.27
Shipping weight (kg)	1.03
Unit Dimensions (HWD/in)	1.54 x 2.72 x 10.3
Unit Dimensions (HWD/cm)	3.91 x 6.91 x 26.16
Shipping Dimensions (HWD/in)	12.40 x 7.09 x 1.77
Shipping Dimensions (HWD/cm)	31.50 x 18.01 x 4.50
Unit weight (lbs)	2.13
Unit weight (kg)	0.97
Material of construction	Plastic
Integrated keyhole mounting tabs	Keyhole mounting slots enable wall mounting
Housing Color	gray
Receptacle Color	gray
AC line cord color	gray
Style	Strip
Outlets center to center measurement	Between Standard Outlets = 29mm; Between Transformer Outlets = 48mm
Keyhole slot center to center measurement	Distance between slots = 78mm; Distance between slot height = 24mm
<b>SPECIAL FEATURES</b>	
Right-Angle Plug	Yes
<b>CERTIFICATIONS</b>	
UL1449 3rd Edition (AC Suppression)	UL1449 3RD EDITION
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
cUL / CSA (Canada)	cUL
Industry Canada (Communications)	Industry Canada
Approvals	Exceeds IEEE 587 category A&B specifications
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$75,000 <a href="#">Ultimate Lifetime Insurance</a>

---

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=134](http://www.tripplite.com/en/products/model.cfm?txtModelID=134).

---

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.