



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: TLM606NC

Power It! Power Strip with 6 Outlets and 6-ft. Cord



Highlights

- 6 outlets
- Illuminated on/off switch with cover
- 15-amp circuit breaker
- 6 ft. power cord
- Rugged metal case
- Keyhole mounting slots

Description

Tripp Lite's Power It! TLM606NC power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment. Includes 6 NEMA 5-15R outlets, 6-foot AC power cord and keyhole mounting slots. Multi-outlet strip reduces cable clutter and enables the connection of multiple electrical devices to a single AC wall socket. Features rugged metal case to stand up to the most demanding environments, illuminated power switch with transparent cover to prevent accidental shutoff and 15A integrated circuit breaker to prevent dangerous overloads.

INPUT/OUTPUT: Input: NEMA 5-15P/Output: 6 NEMA 5-15R

ELECTRICAL: 120V AC, 50/60Hz, 15A

FORMAT: Corded power distribution strip

Applications

- Offers a reliable, convenient and cost-effective method of power distribution for appliances, power tools, lighting and other electrical equipment in home, office or worksite.
- Unfiltered electrical pass-through makes the power strip ideal for distributing alternate waveform UPS or generator power to connected equipment.

Package Includes

- TLM606NC power strip
- Warranty information
- Instruction manual

Features

- Multi-outlet power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment
- Includes 6 NEMA 5-15R outlets
- Illuminated on/off switch provides one-touch power control for connected equipment
- Transparent switch cover snaps tight to prevent accidental shutoff
- Convenient keyhole slots provide secure mounting options for a wide variety of surfaces and applications

- 15A power handling capacity with integrated circuit breaker
- 120V AC, 50/60Hz electrical compatibility
- 6-foot AC line cord
- Rugged metal case provides extra safety and durability
- UL certification

Specifications

OUTPUT	
Frequency compatibility	50 / 60 Hz
Output watts	1800
Circuit Breaker (amps)	15
Overload protection	15A circuit breaker
Outlet quantity / type	6 NEMA 5-15R
Outlet orientation	Single row of 6
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input connection type	NEMA 5-15P
Input cord length (ft.)	6
Input cord length (m)	1.8
Input cord gauge, type	SJT 14AWG
Voltage compatibility (VAC)	120
LEDS ALARMS & SWITCHES	
Switches	Illuminated on/off switch controls power to all outlets
Locking switch cover	Transparent switch cover snaps tight to prevent accidental shutoff
PHYSICAL	
Shipping weight (lbs)	2.2
Shipping weight (kg)	1.00
Unit Dimensions (HWD/in)	13.75 x 2.75 x 2
Unit Dimensions (HWD/cm)	34.92 x 6.99 x 5.08
Shipping Dimensions (HWD/in)	15 x 4.75 x 2.25
Shipping Dimensions (HWD/cm)	38.1 x 12.07 x 5.72
Unit weight (lbs)	2
Unit weight (kg)	0.91
Material of construction	Metal case

Integrated keyhole mounting tabs	Keyhole mounting tabs enable mounting to a variety of surfaces
Receptacle Color	Light Gray
AC line cord color	Light Gray
Outlets center to center measurement	41.30mm
Keyhole slot center to center measurement	Distance between keyhole slots = 203.20mm; Distance between end tabs = 330.17mm
CERTIFICATIONS	
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=3311.

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.