



Protect It! 6-Outlet Industrial Safety Surge Protector, 15-ft. Cord, 2700 Joules, Cord Wrap, Hang Holes

MODEL NUMBER: TLM615SA



Highlights

- 6 outlets (including transformer outlets and 4 safety covers)
- 15 ft. cord
- 2700 joule rating
- Cord wrap with hang holes
- Rugged metal case

Package Includes

- TLM615SA Safety Surge Suppressor
- 4 safety covers
- Owner's manual

Description

This Tripp Lite surge suppressor is designed to provide safe, reliable surge protection. A high 2700 joule rating can protect connected equipment against even the strongest surges. 6 outlets protect connected equipment against damaging surges, spikes and line noise. Convenient transformer outlets accommodate multiple transformers without blocking other outlets. A 15 ft. grounded cord with integrated cord clip reaches distant outlets. A lighted on/off switch with integrated circuit breaker provides power control over connected equipment. Breaker protects against dangerous system overload. Protected LED confirms that connected equipment is being protected. 4 safety covers shield unused outlets from debris and accidental contact. Built-in cord wrap with hang holes provides convenient cord management. Integrated keyhole slots on bottom panel provide convenient wall/desk mounting. Tripp Lite will repair or replace any connected equipment damaged by surges, including direct lightning strikes, up to \$75,000 and for life! As an added safety feature, the surge suppressor's bright yellow color alerts you and others that power cords and tools are in use.

Features

- 6 OUTLETS protect connected equipment against damaging surges, spikes and line noise
- 15 FT. GROUNDED CORD with INTEGRATED CORD CLIP reaches distant outlets.
- LIGHTED ON/OFF SWITCH with INTEGRATED CIRCUIT BREAKER provides power control over connected equipment. Breaker protects against dangerous system overload.
- PROTECTED LED - If this green LED ever goes out, Tripp Lite will replace your surge suppressor under warranty at no charge!
- CONVENIENT TRANSFORMER OUTLETS accommodate multiple transformers without blocking other outlets.
- 4 SAFETY COVERS shield unused outlets from debris and accidental contact.



- RUGGED METAL CASE stands up to harsh indoor use
- CORD WRAP with HANG HOLES provides convenient cord management.
- INTEGRATED KEYHOLE SLOTS on bottom panel provide convenient wall/desk mounting.
- 2700 joules of surge protection
- OSHA color guidelines, outlined in Document 1910.145, alert users to hazardous situations, which may cause minor or moderate injury. This Tripp Lite product complies with those guidelines.
- \$75,000 ULTIMATE LIFETIME INSURANCE (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications

OVERVIEW	
UPC Code	037332140081
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	90000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	15
Right-Angle Plug	No
Input Cord Length (m)	4.57
Integrated Cord Clip	Yes
OUTPUT	
Frequency Compatibility	60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Overload Protection	Combo power switch and circuit breaker
Transformer Accommodation	(4) Yes
Outlet Orientation	6 in a single row
Right-Angle Outlets	No



USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and 2 position lighted on/off power switch
Diagnostic LED Details	1 green "protected" LED confirms surge suppression is present
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	2700
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	400,400,500
EMI / RFI Filtering	Up to 20 dB
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Antimicrobial Coating	No
Color	Black; Yellow
Color (AC Line Cord)	Yellow
Integrated Keyhole Mounting Slots	Yes
Keyhole Slot Mounting Measurement (Center to Center)	209.55mm
Material of Construction	Metal
Outlets Measurement (Center to Center)	Distance between standard outlets = 30.40mm; Distance between standard and transformer outlets = 45mm
Receptacle Color	Black
Shipping Dimensions (hwd / cm)	21.08 x 40.64 x 17.78
Shipping Dimensions (hwd / in.)	8.30 x 16.00 x 7.00
Shipping Weight (kg)	1.68
Shipping Weight (lbs.)	3.70
Unit Dimensions (hwd / cm)	40.56 x 7.80 x 4.09
Unit Dimensions (hwd / in.)	15.97 x 3.07 x 1.61
Unit Weight (kg)	1.47



Unit Weight (lbs.)	3.24
SPECIAL FEATURES	
Rotatable Outlets	No
STANDARDS & COMPLIANCE	
Approvals	cULus, RoHS
UL1449 3rd Edition (AC Suppression)	UL1449 3rd EDITION
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$75,000 Ultimate Lifetime Insurance

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://products/product-certification-agencies>