



## Protect It! Surge Protector with 6 Outlets (2-fixed, 4-rotatable), 6-ft. Cord, 1440 Joules, Tel/Modem/Coax Protection

MODEL NUMBER: TLP606RNET



### Highlights

- 6 outlets - 4 rotate, 2 standard
- 6 ft cord
- 1440 joules
- 1 line tel/modem and 1-line gold coax (2.2GHz bandwidth) protection

### Package Includes

- TLP606RNET Surge Suppressor
- Instruction manual with warranty information
- 6 ft. gold coaxial cable
- 6 ft. phone cord
- 6 ft network cord

### Description

Tripp Lite's TLP606RNET Surge Suppressor provides high-performance protection--1440 joules--stopping damaging surges and filtering disruptive line noise so components perform at their peak! 6 outlets - 4 that rotate, 2 that are standard, 1-line coaxial protection - that also rotates and 1-line tel/modem for maximum protection. \$150,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only). Includes two diagnostic LEDs, 6 ft. gold coaxial cable, 6ft network cable and 6 ft. phone cord.

### Features

- 6 outlets - 4 rotate, 2 standard, allow for easier plug connection and removal
- 1440 joules surge suppression rating with EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans)
- 6ft cord
- 1 set of surge-protected gold coaxial connectors (with included 6 ft. coaxial cable) safeguard components on cable, satellite or antenna line (2.2GHz bandwidth)
- 1 set of surge-protected tel/modem.ethernet connectors (with included 6 ft. phone cord and 6ft Network cable)
- 2 diagnostic LEDs alert user to protection and grounding status
- High-impact plastic housing (black) stands up to the most demanding environments
- \$150,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

## Specifications



<b>OVERVIEW</b>	
UPC Code	037332178244
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	Yes
Input Cord Length (m)	1.83
Integrated Cord Clip	No
<b>OUTPUT</b>	
Frequency Compatibility	60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(4) Yes
Outlet Orientation	Rotatable
Right-Angle Outlets	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Diagnostic LED(s)	Yes
Diagnostic LED Details	Built-in LEDs confirm suppressor "protected" (green) and "grounded" (red) status
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	1440
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
Clamping Voltage (RMS)	300
UL1449 Let Through Rating	400, 500, 500
EMI / RFI Filtering	150 kHz to 100 mHz
Automatic Shut-Off	Yes



<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	1 line
Network (Ethernet) Protection	Yes
<b>PHYSICAL</b>	
Antimicrobial Coating	No
Color	Black
Color (AC Line Cord)	Black
Integrated Keyhole Mounting Slots	No
Material of Construction	Plastic
Receptacle Color	Black; gray
Shipping Dimensions (hwd / cm)	5.08 x 15.49 x 32.77
Shipping Dimensions (hwd / in.)	2.00 x 6.10 x 12.90
Shipping Weight (kg)	1.04
Shipping Weight (lbs.)	2.30
Unit Dimensions (hwd / cm)	5.6 x 15 x 12
Unit Dimensions (hwd / in.)	2.2 x 5.91 x 4.72
Unit Weight (kg)	1.01
Unit Weight (lbs.)	2.22
<b>COMMUNICATIONS</b>	
Network Speed	10/100 Mbps
<b>SPECIAL FEATURES</b>	
Rotatable Outlets	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Canada	cUL
Approvals	RoHS
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$150,000 <a class="insuranceLink" href="/ Insurance</a>&nbsp;	support/insurance-policy">Ultimate Lifetime
---	---	---

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

[https://  
products/product-certification-agencies](https://products/product-certification-agencies)