




## TAA-Compliant Protect It! 8-Outlet Computer Surge Protector, 8-ft. Cord, 3150 Joules, Tel/Modem/Fax Protection

MODEL NUMBER: TLP808TELTAA



### Highlights

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- 8 outlets / 8-ft. cord
- 3150 joule rating
- Modem/fax surge protection

### Package Includes

- TLP808TELTAA Surge Suppressor
- 6-ft. telephone cord
- Instruction manual with warranty information

### Description

Tripp Lite's TLP808TELTAA surge suppressor is compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases. It has 8 outlets, an 8-ft. cord with a space-saving right-angle plug, and diagnostic LEDs. The unit has a surge suppression rating of 3150 joules to handle the strongest surges. Built-in RJ11 jacks prevent surges from damaging your modem/fax/phone equipment. \$150,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

### Features

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- 8 outlets with integrated child safety covers
- 8-ft. cord with space-saving right-angle plug
- Built-in RJ11 jacks (1 in/2 out) prevent surges from damaging your modem/fax/phone equipment; 6-ft. telephone cord included
- Surge suppression rating: 3150 joules
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required
- EMI/RFI noise filtering
- Can accommodate up to 3 transformers without blocking remaining outlets
- \$150,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Diagnostic LEDs indicate protection present & ground present
- Keyhole supports for wall mounting
- Lighted power switch



## Specifications

<b>OVERVIEW</b>	
UPC Code	037332159267
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	8
Right-Angle Plug	Yes
Input Cord Length (m)	2.44
Integrated Cord Clip	No
<b>OUTPUT</b>	
Frequency Compatibility	60 Hz
Output (Watts)	1800
Output Receptacles	(8) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(6) Yes
Outlet Orientation	Single row of 5, plus a second row of 3 for transformer accommodation
Right-Angle Outlets	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and 2-position red illuminated on/off power switch
Diagnostic LED Details	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	3150
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	400 L-N, 500 L-G, 500 N-G
EMI / RFI Filtering	Up to 40 dB



Automatic Shut-Off	Yes
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
<b>PHYSICAL</b>	
Antimicrobial Coating	No
Color	Light Gray
Color (AC Line Cord)	Light Gray
Integrated Keyhole Mounting Slots	Yes
Material of Construction	Plastic
Receptacle Color	Light gray
Shipping Dimensions (hwd / cm)	28.70 x 18.80 x 6.35
Shipping Dimensions (hwd / in.)	11.30 x 7.40 x 2.50
Shipping Weight (kg)	0.91
Shipping Weight (lbs.)	2.00
Unit Dimensions (hwd / cm)	9.8 x 5.6 x 26.6
Unit Dimensions (hwd / in.)	3.9 x 2.2 x 10.5
Unit Weight (kg)	0.59
Unit Weight (lbs.)	1.3
<b>SPECIAL FEATURES</b>	
Additional Information	Pair of phone line output jacks serve as a line splitter to enable the protection of two devices sharing a single dialup phone line
Rotatable Outlets	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Canada	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
UL1449 3rd Edition (AC Suppression)	UL1449 3RD EDITION
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
Industry Canada (Communications)	Industry Canada



WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$150,000 <a class="insuranceLink" href="/support/insurance-policy">Ultimate Lifetime Insurance</a>

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

[https:// products/product-certification-agencies](https://products/product-certification-agencies)