



Dual-Port USB Car Charger for Tablets and Cell Phones, 5V 4.8A (24W)

MODEL NUMBER: U280-C02-S2



Auto-sensing USB ports allow you to charge 2 mobile devices, such as a tablet and cell phone, in your vehicle at the same time.

Description

The U280-C02-S2 Dual-Port USB Car Charger lets you quickly and safely charge two USB-powered mobile devices in your vehicle at the same time. You and your passenger can connect your cell phones simultaneously to ensure full charges when you reach your destination. Also recommended for tablets, MP3 players and other USB devices, the U280-C02-S2 features two 5V 2.4A USB ports. The auto-sensing ports automatically adjust to the appropriate power level and platform, whether your device is an Apple, Android or other. This ultra-compact charger works with any standard 12V DC vehicle power outlet.

Features

Charge 2 Mobile Devices in Your Vehicle at the Same Time

- Recommended for cell phones, tablets, e-readers and MP3 players
- Each USB port supports up to 5V 2.4A
- Auto-sensing ports adjust to appropriate power level and platform (Apple, Android, etc.)
- Works with any standard 12V DC vehicle power outlet

Specifications

OVERVIEW	
UPC Code	037332196316
Product Type	Car Charger
Charging Form Factor	Direct Plug-In

Highlights

- Recommended for cell phones, tablets, e-readers and MP3 players
- Each USB port supports up to 5V 2.4A
- Auto-sensing ports adjust to appropriate power level
- Compatible with Apple, Android and other platforms
- Works with any standard 12V DC vehicle power outlet

Package Includes

- U280-C02-S2 Dual-Port USB Car Charger for Tablets and Cell Phones, 5V 4.8A (24W)



Device Compatibility	Phone; Tablet; Amazon Kindle
INPUT	
Nominal Input Voltage(s) Supported	12V DC
Input Plug Type	Car Auxiliary Power Outlet
OUTPUT	
Output Capacity	24W
Overload Protection	Yes
CHARGING	
Charging Ports / Amps	(2) 2.4A
Number of Charging Ports	2
Total Charging Amps	4.8A
Charging Method	USB
Total Charging Watts	24
Charging Ports Detail	USB-A: 5V/2.4A
Charging Port Type	(2) USB A (FEMALE)
PHYSICAL	
Color	White
Shipping Dimensions (hwd / cm)	1.27 x 8.13 x 11.18
Shipping Dimensions (hwd / in.)	0.50 x 3.20 x 4.40
Shipping Weight (kg)	0.03
Shipping Weight (lbs.)	0.07
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)
Operating Humidity Range	30% to 90% RH, Non-Condensing
Storage Humidity Range	10% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	Car Cigarette Lighter
Side B - Connector 1	(2) USB A (FEMALE)
FEATURES & SPECIFICATIONS	
Technology	USB



SPECIAL FEATURES	
Overcurrent Protection	Yes
Overvoltage Protection	Yes
GaN Technology	No
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: [https:// products/product-certification-agencies](https://products.product-certification-agencies)