



4-Port USB-C Hub with Power Delivery, USB-C to 4x USB-A Ports, USB 3.0, Black

MODEL NUMBER: U460-004-4AB-C



USB 3.1 Type-C hub adds USB-A and USB-C charging ports to your laptop, MacBook, Chromebook or other compatible device.

Features

USB 3.1 Type-C Hub Connects to Your Device's USB-C or Thunderbolt 3 Port

This USB-C hub with PD Charging expands the potential of your tablet, laptop, Chromebook, MacBook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for adding a thumb drive and other USB peripherals or powering and charging a PD Charging-compliant mobile device—all at the same time.

Connects Up to 4 USB-A Peripherals

Four USB-A ports accept USB peripherals, such as a flash drive, mouse, keyboard or printer, and the dedicated USB-A fast-charging port provides up to 5V/1.5A (7.5W) for charging smartphones and other mobile devices. All ports support fast USB 3.1 Gen 1 data transfer rates up to 5 Gbps and are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices.

Charges a Connected Device

The USB-C Power Delivery (PD) port provides power and charging to the PD Charging-compliant device (such as a MacBook, Chromebook or Android smartphone) the USB-C hub is connected to. Connect the device's AC wall charger to the USB-C PD port, which supports power input up to 60W.

Built-In USB-C Cable Connects in Either Direction

Connect the reversible USB-C plug to your source device's Thunderbolt 3 or USB Type-C connector. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

Ready to Use Right Out of the Package

The plug-and-play USB 3.1 Type-C hub requires no software, drivers or external power. The compact unit fits easily into a pocket, briefcase or laptop bag for connecting on the go.

3-Year Warranty and Environmentally Responsible Design

The U460-004-4AB-C comes with a 3-year warranty. It's manufactured in compliance with strict RoHS specifications, reflecting Tripp Lite's commitment to environmental responsibility.

Highlights

- Supports USB 3.1 Gen 1 for fast data transfers up to 5 Gbps
- Accepts up to 4 USB peripherals, turning your laptop into a mini workstation
- USB-A fast-charging port provides up to 5V/1.5A (7.5W) of fast-charging power.
- Powers and charges PD Charging-compliant devices, such as MacBooks and Chromebooks
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Easy installation with plug-and-play operation—no software required

Applications

- Charge your notebook or laptop by connecting its wall charger to the USB-C PD Charging port
- Transfer files to and from a USB thumb drive or external hard drive
- Attach a USB headset/microphone for recording your podcast
- Write a report using a USB keyboard with your tablet or Android smartphone

System Requirements

- Tablet, laptop, Chromebook, MacBook, smartphone or PC with USB-C or Thunderbolt 3 port



Package Includes

- U460-004-4AB-C 4-Port USB 3.1 Hub, 4x USB-A, Thunderbolt 3—PD Charging, Black
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332209214
Host Connector	USB C (MALE)
INPUT	
Built-In Cable Length (ft.)	0.36
Built-In Cable Length (m)	0.11
Built-In Cable Length (in.)	4.33
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m.)	0.15
BATTERY	
Battery Charging (5V/1.5A Port)	Yes
CHARGING	
Charging Ports / Amps	1.5A; 3A
USB Power Delivery (PD) Charging Support	Yes
Total Charging Watts	60
PHYSICAL	
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.9mm
Color	Black
Material of Construction	Plastic
Shipping Dimensions (hwd / in.)	0.90 x 3.90 x 5.60



Shipping Weight (lbs.)	0.10
Unit Dimensions (hwd / in.)	0.43 x 3.7 x 1.6
Unit Packaging Type	Box
Unit Weight (kg)	0.05
Unit Weight (lbs.)	0.1
Wire Gauge (AWG)	28/34
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 °F (0 to 45 °C)
Storage Temperature Range	14 to 158 °F (-10 to 70 °C)
Relative Humidity	10% to 90% RH, Non-Condensing
BTUs	7.5 BTU/Hr
Power Consumption (Watts)	2.2
Power Provided to Connected Device(s)	Up to 20V 3A (60W) Input (USB-C), 5V 1.5A (7.5W) Output USB port, 5V 0.9A (4.5W) Output per USB port
CONNECTIONS	
Ports	5
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	(4) USB 3.0 A (FEMALE)
Side B - Connector 2	USB Type-C (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
UASP Support	No
Technology	USB; USB 3.0 (SuperSpeed); USB 3.1 (Gen 1); PD Charging
STANDARDS & COMPLIANCE	
Certifications	CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:



[https:// products/product-certification-agencies](https://products.product-certification-agencies)