

# Cat5e 350MHz Bulk Stranded-Core PVC Cable - Gray, 1000-ft.

MODEL NUMBER: **N020-01K-GY**



## Description

Tripp Lite's 1,000-ft. gray category 5e (Cat5e) stranded PVC bulk cable is best suited for patch (outside wall) cabling applications. This 24 AWG 4-pair stranded UTP cable has a PVC jacket and is rated for 350MHz/1Gbps communication. Transition speed rating up to 100Mbps. meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 5e draft 11).

## Features

- Designed for patch(outside wall) cabling applications
- Cabling for category 5(Cat5) and 5e(Cat5e) applications
- Length: 1,000 ft. Color: gray
- 24 AWG 4-pair stranded UTP cable with PVC CMR jacket
- Rated for 350MHz/ 1Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL(category 5e draft 11)
- Available in other lengths
- Available in solid copper cable([N022-01K-GY](#)), in plenum cable([N024-01K](#)) and in Cat6([N222-01K](#) and [N224-01K](#))

## Specifications

INPUT	
Cable Length (ft.)	1000
Cable Length (m)	304.80
PHYSICAL	
Color	Gray
CONNECTIONS	
Side A - Connector 1	BARE WIRE
Side B - Connector 1	BARE WIRE
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

## Highlights

- Premium cabling for Category 5 and 5e applications — rated for 350 MHz/1Gbps communications
- 4pr Stranded PVC CMR Jacket

## System Requirements

- For making patch cables for Network Installations 1000 Base-T (1Gbps Ethernet), 10/100 Base-T (Ethernet), 100Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring Type 3 applications.

## Package Includes

- 1000-ft. Cat5e Gray Bulk Patch Cable Stranded PVC 24AWG 350MHz