




## 3 and 4-Wire *minifast*® Cordsets, Standard

- Straight Male Connectors
- NEMA 1, 3, 4, 6P and IEC IP 67 Protection
- 300 V, 9 A



Housing Style	Part Number	Cable	Features	Pinout	
	RSM 31-*M/S816	AWM PVC Yellow 3x20 AWG 105°C 5.2 mm OD Cable #RF50674-*M <sup>†</sup>	<i>flexlife</i>	1. BK 2. BN 3. BU	
	RSM 40-*M	AWM PVC Yellow 4x18 AWG 105°C 7.3 mm OD Cable #RF50548-*M <sup>†</sup>	<i>flexlife</i> ®		
	RSM 40-*M/S90	AWM PUR Yellow 4x18 AWG 105°C 7.3 mm OD Cable #RF50544-*M <sup>†</sup>	<i>Cut/Abrasion Immune</i>		
	RSM 40-*M/S101	AWM TPE Yellow 4x18 AWG 105°C 7.2 mm OD Cable #RF50968-*M <sup>†</sup>	<i>flexlife-10, High Flex - Over 10 million cycles</i>	1. BN 2. WH 3. BU 4. BK	
	RSM 40-*M/S529	PUR Yellow 4x20 AWG 105°C 5.7 mm OD Cable #RF50526-*M <sup>†</sup>	<i>Cut/Abrasion Immune, Braided Mechanical Shield</i>		
	RSM 40-*M/S600	SJOOW CPE Yellow 4x18 AWG 105°C 8.5 mm OD Cable #RF50644-*M <sup>†</sup>	<i>Weld Flash Immune, Flame Immune</i>		
	RSM 40-*M/S824	ITC PLTC PVC Yellow 4x18 AWG 105°C 7.2 mm OD Cable #RF50844-*M <sup>†</sup>	<i>flexlife</i>		

\* Length in Meters. Standard cable lengths are 2, 4, 5, 6, 8 and 10 meters. Consult factory for other lengths. Standard coupling nut material is nickel plated brass "RSM .."; "RS .." indicates nylon and "RSV .." indicates 316 stainless steel.

<sup>†</sup> See Section N for *reelfast*® cable information.

## 3 and 4-Wire *minifast*® Cordsets, Standard

- Straight Female Connectors
- NEMA 1, 3, 4, 6P and IEC IP 67 Protection
- 300 V, 9 A



Housing Style	Part Number	Cable	Features	Pinout
	RKM 31-*M/S816	AWM PVC Yellow 3x20 AWG 105°C, 5.2 mm OD Cable #RF50674-*M <sup>†</sup>	<i>flexlife</i>	1. BK 2. BN 3. BU 
	RKM 40-*M	AWM PVC Yellow 4x18 AWG 105°C 7.3 mm OD Cable #RF50548-*M <sup>†</sup>	<i>flexlife</i> ®	
	RKM 40-*M/S90	AWM PUR Yellow 4x18 AWG 105°C 7.3 mm OD Cable #RF50544-*M <sup>†</sup>	<i>Cut/Abrasion Immune</i>	
	RKM 40-*M/S101	AWM TPE Yellow 4x18 AWG 105°C 7.2 mm OD Cable #RF50968-*M <sup>†</sup>	<i>flexlife-10, High Flex - Over 10 million cycles</i>	1. BN 2. WH 3. BU 4. BK 
	RKM 40-*M/S529	PUR Yellow 4x20 AWG 105°C 5.7 mm OD Cable #RF50526-*M <sup>†</sup>	<i>Cut/Abrasion Immune, Braided Mechanical Shield</i>	
	RKM 40-*M/S600	SJOOW CPE Yellow 4x18 AWG 105°C 8.5 mm OD Cable #RF50644-*M <sup>†</sup>	<i>Weld Flash Immune, Flame Immune</i>	
	RKM 40-*M/S824	ITC PLTC PVC Yellow 4x18 AWG 105°C 7.2 mm OD Cable #RF50844-*M <sup>†</sup>	<i>flexlife</i>	

\* Length in Meters. Standard cable lengths are 2, 4, 5, 6, 8 and 10 meters. Consult factory for other lengths. Standard coupling nut material is nickel plated brass "RKM .."; "RK .." indicates nylon and "RKV .." indicates 316 stainless steel.  
<sup>†</sup> See Section N for *reelfast*® cable information.