

ACCESSORIES

In-Cabinet Power Supplies

- 2.5, 5, 10 and 20 Amp Current Available
- Universal Operating Voltage
- Single/parallel Operation
- IP20

Housing Style	Part Number	Protocol
	<p>IM82-24-10</p>	<p>Power Supply</p>
	<p>IM82-24-20</p>	<p>Power Supply</p>

DISTRIBUTED I/O SALES GUIDE



Pictures represent a sampling of housings

Connector/Gland Material	Housing Material	Certifications	Notes
Nylon	Aluminum	UL, CE	24 VDC, 10A supply, IP20
Nylon	Aluminum	UL, CE	24 VDC, 20A supply, IP20



Accessories