

# NETWORK WIRING

## DeviceNet™, Conduit Adapters

- Converts Standard Conduits to Quick Disconnect
- Fiberglass Reinforced Nylon Housings
- Nickel Plated Brass Connectors Available
- Gasket and Mounting Screws Provided
- IP67



| Housing Style | 1-Port Part Number | 2-Port Part Number | Specifications   | Pinouts |
|---------------|--------------------|--------------------|--|---------|
|               | BCA-57-E123        | BCA-57-E223        | 3/4" Form 8 or Mark 9 conduit to M12x1 adapter, -30°C to +80°C (-22°F to +176°F) |         |
|               | BCA-57-M123        | BCA-57-M223        | 3/4" Form 8 or Mark 9 conduit to 7/8"-16UN, -40°C to +75°C (-40°F to +167°F)     |         |
|               | BCA1-F7-57-M123    | BCA1-F7-57-M223    | 1" Form 7 Conduit Adapter, -40°C to +75°C (-40°F to +167°F)                      |         |

## DeviceNet™, Wall Plate Adapters

- Attaches to Standard Single Gang Electrical Box
- Stainless Steel with Stainless Steel Connectors
- Gasket and Mounting Screws Provided
- IP67



| Housing Style | M12x1 Part Number | 7/8-16UN Part Number | Specifications                               | Pinouts |
|---------------|-------------------|----------------------|--|---------|
|               | BPA-57-E113       | BPA-57-M113          | IP67 rated, -40°C to +75°C (-40°F to +167°F) | <br>    |