

Input Station



FAS4-S0400



- Rugged, Fully Potted Stations
- IP 67 Protection
- Flat and Round Cable Support
- AS-I Version 2.1

Electrical

- Operating Current: <75 mA plus input currents (from AS-I)
- Sensor Current: <200 mA sum of all inputs (from AS-I)

Power Distribution

- Inputs: AS-I power supply

Mechanical

- Operating Temperature: -25 to +70°C (-25 to +158°F)
- Protection: IEC IP 67
- Vibration: 50 g @ 10-500 Hz

Material

- Connectors: Nickel-plated brass
- Housing: Nylon 6

Diagnostics (Logical)

- I/O faults are reported via the AS-I peripheral fault bit.

