

TURCK

Process Wiring Products

minifast® lokfast® Guards

Part Number	Application
LOCK-MINI	<i>Nylon locking guard for straight minifast standard body connectors (RKM, RKV, RSM and RSV) in Class I, Division 2 installations*</i>
LOCK-MINI (10/BAG)	
LOCK-MINI-ANGLE	<i>Nylon locking guard for right angle minifast standard body connectors (WKM, WKV, WSM and WSV) in Class I, Division 2 installations*</i>
LOCK-MINI-ANGLE (10/BAG)	
LOCK-MINI-FW	<i>Nylon locking guard for straight minifast field wireable connectors (BS 41..., and B 41...) in Class I, Division 2 installations*</i>
LOCK-MINI-FW (10/BAG)	
LOCK-MINI-B&C	<i>Nylon locking guard for straight minifast "B" Style and "C" Style connectors (RKM, RKV, RSM and RSV) in Class I, Division 2 installations*</i>
LOCK-MINI-B&C (10/BAG)	
LOCK-MINI-B&C-ANGLE	<i>Nylon locking guard for right angle minifast "B" Style and "C" Style connectors (WKM, WKV, WSM and WSV) in Class I, Division 2 installations*</i>
LOCK-MINI-B&C-ANGLE (10/BAG)	



lokfast Closed



lokfast Open

eurofast® lokfast® Guards

Part Number	Application
LOCK-EURO-G	<i>Nylon locking guard for straight eurofast G-body connectors (RKG, RKGV, RSG and RSGV) in Class I, Division 2 installations*</i>
LOCK-EURO-G (10/BAG)	
LOCK-EURO-R	<i>Nylon locking guard for straight eurofast R-body connectors (RKR, RKR, RSR and RSRV) in Class I, Division 2 installations*</i>
LOCK-EURO-R (10/BAG)	
LOCK-EURO-FW	<i>Nylon locking guard for straight eurofast field wireable connectors (B81.., BS81.. and BM81..) in Class I, Division 2 installations*</i>
LOCK-EURO-FW (10/BAG)	



lokfast Open



lokfast Closed

* See TURCK Control Drawing QCF-00147 (FM) or Ni-2.404 (CSA) at www.turck.com/fmcd/ for guidance on installation in hazardous locations.