



Housing Style	Part Number	Output
<p>21 mm Anodized Aluminum, 6-pin <i>euofast</i>® Connection</p>	LT***E-Q21D-RS-X3-H1161	RS 422 Start/Stop pulse
	LT***E-Q21D-VPI***-X3-H1161	Variable pulse internal interrogations
	LT***E-Q21D-VPE-X3-H1161	Variable pulse external interrogations
<p>21 mm Anodized Aluminum, 12-pin <i>euofast</i> Connection</p>	LT***E-Q21-DQR*N*X2-H11121	Quadrature RS 422 Line Driver (TTL)
	LT***E-Q21-DQR*N*X2-H11121	Quadrature RS 422 Line Driver (TTL)
	LT***E-Q21-DQL*N*X2-H11121	Quadrature 10-30 VDC Line Driver
	LT***E-Q21-DQL*N*X2-H11121	Quadrature 10-30 VDC Line Driver
	LT***E-Q21-DQR*V*X2-H11121	Quadrature RS 422 Line Driver (TTL)
	LT***E-Q21-DQR*V*X2-H11121	Quadrature RS 422 Line Driver (TTL)
	LT***E-Q21-DQR*V*X2-H11121	Quadrature 10-30 VDC Line Driver
LT***E-Q21-DQR*V*X2-H11121	Quadrature 10-30 VDC Line Driver	

*** Span = measuring length in inches.

See page L45 for magnets and mounting accessories (not included).

Voltage	Features	Eurofast Connection	Enclosure Rating	Agency Approval	Mating Cordset	Wiring Diagram #	Wiring Diagrams
13.5-30 VDC	Digital Output	6-pin	IP 67	CE	RKS 6T-*	1	<div style="border: 1px solid black; padding: 5px; margin-bottom: 10px;"> Diagram 1 </div> <div style="border: 1px solid black; padding: 5px;"> Diagram 2 </div>
	Digital Output	6-pin	IP 67	CE	RKS 6T-*	1	
	Digital Output	6-pin	IP 67	CE	RKS 6T-*	1	
13.5-30 VDC	Nonvolatile Zero Offset Storage	12-pin	IP 67	CE	RKS 10T-*	2	
	Nonvolatile Zero Offset Storage	12-pin	IP 67	CE	RKS 10T-*	2	
	Nonvolatile Zero Offset Storage	12-pin	IP 67	CE	RKS 10T-*	2	
	Nonvolatile Zero Offset Storage	12-pin	IP 67	CE	RKS 10T-*	2	
	Volatile Zero Offset Storage	12-pin	IP 67	CE	RKS 10T-*	2	
	Volatile Zero Offset Storage	12-pin	IP 67	CE	RKS 10T-*	2	
	Volatile Zero Offset Storage	12-pin	IP 67	CE	RKS 10T-*	2	

* Length in meters.