

19-Pin multifast® Cordsets, DC Color Code, Standard Wiring, M23 Thread

- Right Angle Female Connector
- For eurofast® Junction Boxes and multi-conductor Applications
- IEC IP 67 Protection
- 150 V



Housing Style	Part Number	Cable	Ports, App.	Features	Pinout
	CKWM 19-11-*	PLTC PVC Yellow 3x18, 8x22 AWG 105° C 8.4 mm OD Cable #RF50624-*M†	4-port, 2 Signals per port	flexlife®	
	CKWM 19-11-*/S90	AWM PUR Yellow 3x18, 8x22 AWG 105° C 8.4 mm OD Cable #RF50718-*M†		Cut/Abrasion Immune	
	CKWM 19-15-*	AWM PVC Yellow 3x18, 12x22 AWG 105° C 8.4 mm OD Cable #RF50625-*M†	6-port, 2 Signals per port	flexlife	
	CKWM 19-15-*/S90	AWM PUR Yellow 3x18, 12x22 AWG 105° C 8.4 mm OD Cable #RF50818-*M†		Cut/Abrasion Immune	
	CKWM 19-19-*	PLTC PVC Yellow 3x18, 16x22 AWG 105° C 10.4 mm OD Cable #RF50620-*M†	8 port, 2 Signals per port	flexlife	
	CKWM 19-19-*/S90	AWM PUR Yellow 3x18, 16x22 AWG 105° C 10.4 mm OD Cable #RF50682-*M†		Cut/Abrasion Immune	
	CKWM 19-19-*/S101	AWM TPE Yellow 3x18, 16x22 AWG 105° C 10.4 mm OD Cable #RF50916-*M†		flexlife-10, High Flex - Over 10 million cycles	

* Length in meters.

Standard cable lengths are 5 and 10 meters. Consult factory for other lengths.

Standard coupling nut material is nickel plated brass.. "CKWM.."; "CKWMV.." indicates stainless steel coupling nut.

† See Section N for reelfast® cable information.

19-Pin multifast® Cordsets, DC Color Code, Standard Wiring, M23 Thread

- Straight Male Connector
- For eurofast® Junction Boxes and multi-conductor Applications
- IEC IP 67 Protection
- 150 V



Housing Style	Part Number	Cable	Ports, App.	Features	Pinout
	CSM 19-11-*	PLTC PVC Yellow 3x18, 8x22 AWG 105° C 8.4 mm OD Cable #RF50624-*M†	4-port, 2 Signals per port	flexlife®	
	CSM 19-11-*/S90	AWM PUR Yellow 3x18, 8x22 AWG 105° C 8.4 mm OD Cable #RF50718-*M†		Cut/Abrasion Immune	
	CSM 19-15-*	AWM PVC Yellow 3x18, 12x22 AWG 105° C 8.4 mm OD Cable #RF50625-*M†	6-port, 2 Signals per port	flexlife	
	CSM 19-15-*/S90	AWM PUR Yellow 3x18, 12x22 AWG 105° C 8.4 mm OD Cable #RF50818-*M†		Cut/Abrasion Immune	
	CSM 19-19-*	PLTC PVC Yellow 3x18, 16x22 AWG 105° C 10.4 mm OD Cable #RF50620-*M†	8 port, 2 Signals per port	flexlife	
	CSM 19-19-*/S90	AWM PUR Yellow 3x18, 16x22 AWG 105° C 10.4 mm OD Cable #RF50682-*M†		Cut/Abrasion Immune	
	CSM 19-19-*/S101	AWM TPE Yellow 3x18, 16x22 AWG 105° C 10.4 mm OD Cable #RF50916-*M†		flexlife-10, High Flex - Over 10 million cycles	

* Length in meters.

Standard cable lengths are 5 and 10 meters. Consult factory for other lengths.

Standard coupling nut material is nickel plated brass.. "CSM.."; "CSMV.." indicates stainless steel coupling nut.

† See Section N for reelfast® cable information.