

**Locknuts**

<b>Chrome Plated Brass</b>						
Part Number	ID Number	Barrel Diameter	Dimensions			D
			A	B	C	
Locknut-M05	A3119	5 mm	0.28 [7.0]	0.32 [8.0]	0.10 [2.5]	M5x0.5
Locknut-M08	A3120	8 mm	0.51 [13.0]	0.58 [14.7]	0.16 [4.0]	M8x1
Locknut-M12	A3122	12 mm	0.67 [17.0]	0.76 [19.4]	0.16 [4.0]	M12x1
Locknut-M18	A3125	18 mm	0.94 [24.0]	1.08 [27.4]	0.16 [4.0]	M18x1
Locknut-M30	A3126	30 mm	1.42 [36.0]	1.63 [41.4]	0.20 [5.0]	M30x1.5
Locknut-PG36	A3440	47 mm	2.01 [51.1]	2.20 [56.0]	0.20 [5.0]	PG36
Locknut 1/4-18	A3131	—	0.43"	0.49"	0.22"	1/4-18
Locknut 1/2-14	A3132	—	0.74"	0.85"	0.43"	1/2-14
<b>300 Series Stainless Steel</b>						
Locknut-SS12	A3123	12 mm	0.67 [17.0]	0.76 [19.4]	0.16 [4.0]	M12x1
Locknut-SS18	A3123-0	18 mm	0.94 [24.0]	1.08 [27.4]	0.16 [4.0]	M18x1
Locknut-SS30	A3123-1	30 mm	1.42 [36.0]	1.63 [41.4]	0.20 [5.0]	M30x1.5
<b>PTFE Coated</b>						
Locknut-MT12	A3109	12 mm	0.67 [17.0]	0.76 [19.4]	0.16 [4.0]	M12x1
Locknut-MT18	A3108	18 mm	0.94 [24.0]	1.08 [27.4]	0.16 [4.0]	M18x1
Locknut-MT30	A3107	30 mm	1.42 [36.0]	1.63 [41.4]	0.20 [5.0]	M30x1.5
For use with PTFE coated threaded metal barrel sensors.						
<b>Polyamide Plastic *</b>						
Locknut-P12	A3446	12 mm	0.67 [17.0]	0.75 [19.0]	0.32 [8.0]	M12x1
Locknut-P18	A3448	18 mm	0.94 [24.0]	1.06 [27.0]	0.32 [8.0]	M18x1
Locknut-P30	A3450	30 mm	1.42 [36.0]	1.58 [40.1]	0.39 [10.0]	M30x1.5
For use with threaded plastic barrel sensors. * 5 mm Plastic Nut Material: Delrin Inches [mm]						

