


Inductive Low Temperature Sensors



Housing Style	Part Number	ID Number	Features	Sensing Range (mm)	Output
12 mm - Embeddable, Potted-in Cable 	Bi 2-EM12WD-AP6/S929	M4614515	Washdown, -60°C	2	3-Wire DC PNP
18 mm - Nonembeddable, Potted-in Cable 	Ni 7-EM18WD-AP6X/S929	M4632001	Washdown, -60°C	7	3-Wire DC PNP

For detailed sensor specifications see Section M.
Normally Closed versions available upon request, consult factory.



Voltage	Switching Freq. (Hz)	Operating Current (mA)	Operating Temp. (°C)	Protection	Housing	Face	Power LED	Output LED	Cable Length/ Jacket	Wiring Diagram #	Wiring Diagrams
10-30 VDC	1000	≤200	-60 to +60	IP 68, 69K	SS	PTFE	N/A	N/A	2M/FEP (TFE)	1	<div style="border: 1px solid black; padding: 5px;"> <p style="text-align: center; margin: 0;">Diagram 1</p>  </div>
10-30 VDC	1000	≤200	-60 to +60	IP 68, 69K	SS	PTFE	N/A	RD	2M/FEP (TFE)	1	

Low Temp.

Harsh Duty

* Length in meters.