


**6x18 AWG AWM 21743 90C 300V**

**SPECIFICATIONS**

A	18 AWG 19x.0092" UNILAY TINNED COPPER
B	PVC INSULATION
C	FILLER
D	22 AWG TINNED COPPER DRAIN WIRE
E	ALUMINUM/POLYESTER FOIL SHIELD (FOIL IN)
F	TPU JACKET JACKET COLOR: YELLOW CABLE IS RoHS COMPLIANT

**CONDUCTOR COLORS**

- 1 = GREEN
- 2 = YELLOW
- 3 = GRAY
- 4 = BROWN
- 5 = BLUE
- 6 = WHITE



**MECHANICAL REQUIREMENTS**

STATIC: 5x CABLE O.D.  
FLEX SHIELDED: 15x CABLE O.D.

NOTE: CONDUCTOR ROTATION MAY BE INVERTED FROM VIEW SHOWN **SOURCE DRAWING - FOR REFERENCE ONLY**

**NOTES:**

1. BLACK INK

101550662 18 AWG/6 RU AWM 90C 300V UL# CSA AWM CSA# I/II A/B  
90C 300V FT1 SUPPLIER LOT CODE (WHEN  
APPLICABLE) MFG DATE CODE (EXAMPLE 00108 (DAY & YEAR))

2. c(UL) IS ACCEPTABLE IN PLACE OF ANY/ALL CSA MARKINGS.

RELATED DOCUMENTS		3RD ANGLE PROJECTION		THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		<p>3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax www.turck.us</p> <p><b>TURCK</b></p>	
1. 2. 3. 4.				DRFT CK DATE 07/20/11 APVD SF SCALE NONE		DESCRIPTION CAB,6.73,YEL,TPU,6X18,S-,AWM	
MATERIAL SEE SPECIFICATIONS		ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		UNIT OF MEASUREMENT <b>INCH [ MILLIMETER ]</b>		IDENTIFICATION NO. 101550662 (SOURCE)	
FINISH SEE SPECIFICATIONS		CONTACT TURCK FOR MORE INFORMATION		DO NOT SCALE THIS DRAWING		REV G	
G UPDATED GRN/YEL CONDUCTOR TO GRN PER ECO		TV 08/02/17		61615		FILE: 101550662	
REV DESCRIPTION		BY DATE		ECO NO.		SHEET 1 OF 1	