


6x12 AWG WTTC 90C 1000V/TC-ERDB 90C 600V/ITC/PLTC, ERDB 105C/AWM 2586 105C 600V/CICTC 90C 600V

SPECIFICATIONS

A	12 AWG 65x30 BUNCHED BARE COPPER
B	PVC INSULATION
C	NYLON COVERING
D	FILLER
E	PAPER SEPARATOR
F	PRESSURED TPE JACKET JACKET COLOR: YELLOW (PANTONE 108U OR 107U) CABLE IS RoHS COMPLIANT, CE

CONDUCTOR COLORS

- 1 = BROWN
- 2 = ORANGE
- 3 = YELLOW
- 4 = BLUE
- 5 = RED
- 6 = GREEN/YELLOW



MECHANICAL REQUIREMENTS

STATIC: 5x CABLE O.D.
FLEX NON-SHIELDED: 10x CABLE O.D.

NOTES:

1. BLACK INK

101551059 12 AWG/6 (UL) TC-ER DIRECT BURIAL UL# 90C DRY/WET 600V SUNLIGHT RESISTANT OIL RES I & II OR WTTC 90C DRY/WET 1000V OR ITC-ER DIRECT BURIAL 105C OR PLTC-ER DIRECT BURIAL 105C -40C OR AWM 105C 600V OR CSA CSA# CIC/TC PVC/N 90C DRY 75C WET 600V FT1 FT4 SUNLIGHT RESISTANT CE SUPPLIER LOT CODE (WHEN APPLICABLE) MFG DATE CODE (EXAMPLE 00108 (DAY & YEAR))

2. c(UL) IS ACCEPTABLE IN PLACE OF ANY/ALL CSA MARKINGS

SOURCE DRAWING - FOR REFERENCE ONLY

RELATED DOCUMENTS		3RD ANGLE PROJECTION		THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax www.turck.us	
1. 2. 3. 4.				DRFT RDS DATE 07/19/12 APVD J.H. SCALE NONE		DESCRIPTION CAB,14.73,YEL,TPE,6X12,TCERDB	
MATERIAL SEE SPECIFICATIONS		ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		UNIT OF MEASUREMENT INCH [MILLIMETER]		IDENTIFICATION NO. 101551059 (SOURCE)	
FINISH SEE SPECIFICATIONS		CONTACT TURCK FOR MORE INFORMATION		DO NOT SCALE THIS DRAWING		REV H	
H UPDATED NOTES, SPECS AND CONDUCTOR COLOR PER ECOTV		06/13/17		60717		FILE: 101551059	
REV DESCRIPTION		BY DATE		ECO NO.		SHEET 1 OF 1	