


4x16 AWG WTTC 90C 1000V/TC-ERDB 90C 600V/ITC/PLTC, ERDB 105C/CICTC 90C 600V

SPECIFICATIONS

A	16 AWG 65x34 BUNCHED BARE COPPER
B	PVC INSULATION
C	NYLON COVERING
D	TISSUE PAPER SEPARATOR
E	PVC JACKET JACKET COLOR: YELLOW CABLE IS RoHS COMPLIANT, CE CABLE IS COMPLIANT WITH IEC 60332-3-22

CONDUCTOR COLORS

- 1 = RED
- 2 = WHITE
- 3 = BLACK
- 4 = GREEN/YELLOW



MECHANICAL REQUIREMENTS

STATIC: 5x CABLE O.D.
FLEX NON-SHIELDED: 10x CABLE O.D.

NOTES:

1. BLACK INK

10151220 16 AWG/4 (UL) TC-ER DIR BUR UL# 90C DRY/WET 600V SUN RES OIL RES I OR WTTC 90C DRY/WET 1000V OR ITC-ER DIR BUR 105C OR PLTC-ER DIR BUR 105C -40C OR CSA CSA# CIC/TC PVC/N 90C DRY 75C WET 600V FT1 FT4 SUN RES IEC 60332-3-22 CE SUPPLIER LOT CODE (WHEN APPLICABLE) MFG DATE CODE (EXAMPLE 00108 (DAY & YEAR))

2. c(UL) IS ACCEPTABLE IN PLACE OF ANY/ALL CSA MARKINGS.

SOURCE DRAWING - FOR REFERENCE ONLY

RELATED DOCUMENTS		3RD ANGLE PROJECTION		THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		<p>3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax www.turck.us</p>			
1.			ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY	DRFT	CK	DATE	02/18/11		
2.				APVD	-	SCALE	NONE	DESCRIPTION	CAB,9.14,YEL,PVC,4X16,TCERDB
3.				UNIT OF MEASUREMENT		IDENTIFICATION NO.		REV	
4.				INCH [MILLIMETER]		101551220 (SOURCE)		K	
MATERIAL		SEE SPECIFICATIONS		CONTACT TURCK FOR MORE INFORMATION		DO NOT SCALE THIS DRAWING			
FINISH		SEE SPECIFICATIONS		FILE: 101551220		SHEET 1 OF 1			

K	UPDATE CONDUCTOR TO "GREEN/YELLOW"	RDS	06/28/17	61083
REV	DESCRIPTION	BY	DATE	ECO NO.