


SPECIFICATIONS

A	12 AWG 65x30 BUNCHED BARE COPPER
B	PVC INSULATION
C	NYLON COVERING
D	FILLER
E	ALUMINUM/POLYESTER FOIL SHIELD (FOIL OUT)
F	34 AWG TINNED COPPER BRAIDED SHIELD (65% COVERAGE)
G	PAPER SEPARATOR
H	PRESSURED TPE JACKET JACKET COLOR: YELLOW
	CABLE IS RoHS COMPLIANT, CE CABLE IS COMPLIANT WITH IEC 60332-3-22

CONDUCTOR COLORS

- 1 = BROWN
- 2 = ORANGE
- 3 = YELLOW
- 4 = BLUE
- 5 = RED
- 6 = GREEN/YELLOW



MECHANICAL REQUIREMENTS

STATIC: 5x CABLE O.D.
FLEX SHIELDED: 15x CABLE O.D.

NOTES:

1. BLACK INK

101551286 12 AWG/6 (UL) TC-ER DIRECT BURIAL UL# 90C DRY/WET 600V SUNLIGHT RESISTANT OIL RES I & II OR WTTC 90C DRY/WET 1000V OR ITC-ER DIRECT BURIAL 105C OR PLTC-ER DIRECT BURIAL 105C -40C OR AWM 105C 600V OR CSA CSA# CIC/TC PVC/N 90C DRY 75C WET 600V SHIELDED FT1 FT4 SUNLIGHT RESISTANT IEC 60332-3-22 CE SUPPLIER LOT CODE (WHEN APPLICABLE) MFG DATE CODE (EXAMPLE 00108 (DAY & YEAR))

2. c(UL) IS ACCEPTABLE IN PLACE OF ANY/ALL CSA MARKINGS.

SOURCE DRAWING - FOR REFERENCE ONLY

RELATED DOCUMENTS		3RD ANGLE PROJECTION		THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax www.turck.us	
1. 2. 3. 4.				DRFT RDS DATE 04/01/13 APVD J.H. SCALE NONE		DESCRIPTION CAB,15.49,YEL,TPE,6X12,S-,TCERDB	
MATERIAL SEE SPECIFICATIONS		ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		UNIT OF MEASUREMENT INCH [MILLIMETER]		IDENTIFICATION NO. 101551286 (SOURCE)	
FINISH SEE SPECIFICATIONS		CONTACT TURCK FOR MORE INFORMATION		DO NOT SCALE THIS DRAWING		REV F	
F	UPDATE DRAWING PER ECO	TR	06/27/17	61079			
REV	DESCRIPTION	BY	DATE	ECO NO.	FILE: 101551286	SHEET 1 OF 1	