


2X12 AWG WTTTC 90C 1000V/TC-DB 90C 600V/ITC/PLTC, ERDB 105C/CICTC 90C 600V

SPECIFICATIONS

A	12 AWG 65x30 BUNCHED BARE COPPER
B	PVC INSULATION
C	NYLON COVERING
D	FILLER
E	TISSUE PAPER SEPARATOR
F	PVC JACKET JACKET COLOR: BLACK
CABLE IS RoHS 2 COMPLIANT, CE	
CABLE IS COMPLIANT WITH IEC 60332-3-22	

CONDUCTOR COLORS

- 1 = BLACK
- 2 = WHITE



MECHANICAL REQUIREMENTS

STATIC: 5x CABLE O.D.
FLEX NON-SHIELDED: 10x CABLE O.D.

NOTES:

1. WHITE INK

101551380 12 AWG/2 (UL) TC DIR BUR UL# 90C DRY/WET 600V SUN RES OIL RES I OR WTTTC 90C DRY/WET 1000V OR ITC-ER DIR BUR 105C OR PLTC-ER DIR BUR 105C -40C OR CSA CSA# CIC/TC PVC/N 90C DRY 75C WET 600V FT1 FT4 SUN RES IEC 60332-3-22 -40C COLD BEND CE SUPPLIER LOT CODE (WHEN APPLICABLE) MFG DATE CODE (EXAMPLE 00108 (DAY & YEAR))

2. c(UL) IS ACCEPTABLE IN PLACE OF ANY/ALL CSA MARKINGS

SOURCE DRAWING - FOR REFERENCE ONLY

RELATED DOCUMENTS				3RD ANGLE PROJECTION		THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax www.turck.us	
1. 2. 3. 4.						DRFT CK DATE 02/18/11		DESCRIPTION CAB,10.01,BLK,PVC,2X12,TCDB	
MATERIAL SEE SPECIFICATIONS						APVD - SCALE NONE			
FINISH SEE SPECIFICATIONS				ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY CONTACT TURCK FOR MORE INFORMATION		UNIT OF MEASUREMENT INCH [MILLIMETER]		IDENTIFICATION NO. 101551380 (SOURCE)	
L UPDATE OVERALL TOLERANCE						DO NOT SCALE THIS DRAWING		REV L	
RDS 10/11/17 62642									
REV DESCRIPTION				BY DATE ECO NO.					