


6x18 AWG ITC/PLTC/AWM 2586 105C 600V

SPECIFICATIONS

A	18 AWG 19x.0092" UNILAY TINNED COPPER
B	PVC INSULATION
C	POLY FILLER
D	PAPER SEPARATOR
E	PVC JACKET JACKET COLOR: BLACK CABLE IS RoHS COMPLIANT

CONDUCTOR COLORS

- 1 = GREEN
- 2 = YELLOW
- 3 = GRAY
- 4 = BROWN
- 5 = BLUE
- 6 = WHITE



MECHANICAL REQUIREMENTS

STATIC: 5x CABLE O.D.
FLEX NON-SHIELDED: 10x CABLE O.D.

NOTE: CONDUCTOR ROTATION MAY BE INVERTED FROM VIEW SHOWN

SOURCE DRAWING - FOR REFERENCE ONLY

NOTES:

- WHITE INK
101551641 FLEXLIFE™ AND C-TRACK 18 AWG/6 (UL) ITC 105C UL#
SUNLIGHT RESISTANT OR PLTC 105C -40C OIL RES I & II OR AWM 105C 600V OR
CSA CMX OUTDOOR-CMG CSA# 105C OR CSA AWM I/II A/B 105C 600V FT4
MSHA# SUPPLIER LOT CODE (WHEN APPLICABLE) MFG DATE CODE
(EXAMPLE 00108 (DAY & YEAR))
- c(UL) IS ACCEPTABLE IN PLACE OF ANY/ALL CSA MARKINGS

RELATED DOCUMENTS		3RD ANGLE PROJECTION		THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax www.turck.us	
1. 2. 3. 4.				DRFT RDS DATE 11/03/11 APVD S.F. SCALE NONE		DESCRIPTION CAB,8.38,BLK,PVC,6X18,ITC,FL	
MATERIAL SEE SPECIFICATIONS		ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		UNIT OF MEASUREMENT INCH [MILLIMETER]		IDENTIFICATION NO. 101551641 (SOURCE)	
FINISH SEE SPECIFICATIONS		CONTACT TURCK FOR MORE INFORMATION		DO NOT SCALE THIS DRAWING		REV F	
F	UPDATE DESCRIPTION & NOTES	NF	10/09/18	67098		FILE: 101551641	
REV	DESCRIPTION	BY	DATE	ECO NO.		SHEET 1 OF 1	