


4x12 AWG WTTTC 90C 1000V/TC-ERDB 90C 600V/STOOW 90C 600V/CICTC 90C 600V	
SPECIFICATIONS	
A	12 AWG 65x30 BUNCHED BARE COPPER
B	PVC INSULATION
C	NYLON COVERING
D	FILLER
E	PAPER SEPARATOR
F	TPE JACKET JACKET COLOR: BLACK CABLE IS RoHS COMPLIANT, CE

CONDUCTOR COLORS

- 1 = WHITE
- 2 = RED
- 3 = GREEN/YELLOW
- 4 = BLACK



MECHANICAL REQUIREMENTS

STATIC: 5x CABLE O.D.
FLEX NON-SHIELDED: 10x CABLE O.D.

NOTES:

1. WHITE INK

101551668 12 AWG/4 (UL) TC-ER DIRECT BURIAL UL# 90C DRY/WET 600V SUNLIGHT RESISTANT OIL RES I & II OR WTTTC 90C DRY/WET 1000V OR STOOW 4/C 12 AWG (3.31mm²) 90C -40C 600V FT2 OR CSA CSA# CIC/TC PVC/N 90C DRY 75C WET 600V FT1 FT4 SUNLIGHT RESISTANT CE SUPPLIER LOT CODE (WHEN APPLICABLE) MFG DATE CODE (EXAMPLE 00108 (DAY & YEAR))

2. c(UL) IS ACCEPTABLE IN PLACE OF ANY/ALL CSA MARKINGS.

NOTE: CONDUCTOR ROTATION MAY BE INVERTED FROM VIEW SHOWN **SOURCE DRAWING - FOR REFERENCE ONLY**

RELATED DOCUMENTS		3RD ANGLE PROJECTION		THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		TURCK 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax www.turck.us	
1.			ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY	DRFT	RDS	DATE	07/19/12
2.				APVD	J.H.	SCALE	NONE
3.		UNIT OF MEASUREMENT				IDENTIFICATION NO.	
4.		INCH [MILLIMETER]				101551668 (SOURCE)	
MATERIAL		SEE SPECIFICATIONS		CONTACT TURCK FOR MORE INFORMATION		REV	
FINISH		SEE SPECIFICATIONS		DO NOT SCALE THIS DRAWING		FILE: 101551668 SHEET 1 OF 1	