


3x12 AWG WTTTC 90C 1000/TC-ERDB 90C 600V/ST00W 90C 600V/CICTC 90C 600V

SPECIFICATIONS

A	12 AWG 65x30 BUNCHED BARE COPPER
B	PVC INSULATION
C	NYLON COVERING
D	FILLER
E	PAPER SEPARATOR
F	PRESSURED TPE JACKET JACKET COLOR: BLACK CABLE IS RoHS COMPLIANT, CE

CONDUCTOR COLORS

- 1 = WHITE
- 2 = GREEN/YELLOW
- 3 = BLACK



MECHANICAL REQUIREMENTS

STATIC: 5x CABLE O.D.
FLEX NON-SHIELDED: 10x CABLE O.D.

NOTES:

1. WHITE INK

101551669 12 AWG/3 (UL) TC-ER DIRECT BURIAL UL# 90C DRY/WET 600V SUNLIGHT RESISTANT OIL RES I & II OR WTTTC 90C DRY/WET 1000V OR ST00W 3/C 12 AWG (3.31mm²) 90C -40C 600V FT2 OR CSA CSA# CIC/TC PVC/N 90C DRY 75C WET 600V FT1 FT4 SUNLIGHT RESISTANT CE SUPPLIER LOT CODE (WHEN APPLICABLE) MFG DATE CODE (EXAMPLE 00108 (DAY & YEAR))

2. c(UL) IS ACCEPTABLE IN PLACE OF ANY/ALL CSA MARKINGS.

NOTE: CONDUCTOR ROTATION MAY BE INVERTED FROM VIEW SHOWN **SOURCE DRAWING - FOR REFERENCE ONLY**

RELATED DOCUMENTS		3RD ANGLE PROJECTION		THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax www.turck.us	
1. 2. 3. 4.				DRFT RDS DATE 07/19/12 APVD J.H. SCALE NONE		DESCRIPTION CAB,16.26,BLK,TPE,3X12,TCERDB	
MATERIAL		ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		UNIT OF MEASUREMENT		IDENTIFICATION NO.	
SEE SPECIFICATIONS		CONTACT TURCK FOR MORE INFORMATION		INCH [MILLIMETER] DO NOT SCALE THIS DRAWING		101551669 (SOURCE)	
FINISH						REV	
SEE SPECIFICATIONS						J	
J	UPDATE LEGEND	RDS	10/25/17	62859		FILE: 101551669	
REV	DESCRIPTION	BY	DATE	ECO NO.		SHEET 1 OF 1	