



SPECIFICATIONS	
HOUSING MATERIAL	ALUMINUM ALLOY
HOUSING FINISH/COLOR	POWDER COAT/BLACK
RECEPTACLE HOUSING MAT'L/PLATING	BRASS/NICKEL
CONTACT CARRIER MAT'L/COLOR	TPU BLACK
CONTACT MATERIAL/PLATING	BRASS/GOLD
CABLE JACKET MATERIAL/COLOR	PVC/YELLOW
OPERATING VOLTAGE	250 VAC/300 VDC
OPERATING CURRENT	4.0 A PER PORT, 9.0 A TOTAL
PROTECTION CLASS to DIN 40050	IP 67 - ONLY WHEN ALL RECEPTACLES ARE COVERED WITH PLUGS OR CONNECTED
OPERATING TEMPERATURE	-40°C to +90°C (-40°F to +194°F)



SOURCE DRAWING - FOR REFERENCE ONLY

- NOTES:
- "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.
 - "/CS10067" DESIGNATES SPECIAL WIRING PER CUSTOMER REQUEST.

RELATED DOCUMENTS		3RD ANGLE PROJECTION		THIS DOCUMENT IS PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com	
MATERIAL SEE SPECIFICATIONS		DRFT RDS APVD T.S.		DATE 10/10/18 SCALE 1=2		DESCRIPTION 6RK60-M/CS10067	
FINISH SEE SPECIFICATIONS		UNIT OF MEASUREMENT MILLIMETER [INCH]		IDENTIFICATION NO.		REV A	
A DRAWING RELEASE		RDS 11/14/18		DO NOT SCALE THIS DRAWING		FILE: 777042308	
REV DESCRIPTION		BY DATE ECO NO.		CONTACT TURCK FOR MORE INFORMATION		SHEET 1 OF 1	

A	DRAWING RELEASE	RDS	11/14/18	
REV	DESCRIPTION	BY	DATE	ECO NO.