


FEMALE END VIEW




1 = BROWN	15 = BLUE
2 = WHITE/GREY	16 = BLACK/GREY
3 = BLUE/GREY	17 = BROWN/ORANGE
4 = BROWN/GREY	18 = WHITE/ORANGE
5 = BLACK/YELLOW	19 = BLACK/ORANGE
6 = WHITE/YELLOW	20 = BLACK/GREEN
7 = BLUE/YELLOW	21 = WHITE/GREEN
8 = BROWN/YELLOW	22 = BLUE/GREEN
9 = BLACK/RED	23 = BROWN/GREEN
10 = WHITE/RED	24 = BLUE/ORANGE
11 = BLUE/RED	25 = GREEN/YELLOW
12 = BROWN/RED	26 = N/C
13 = BLACK	
14 = WHITE	

DRAIN/SHIELD

SPECIFICATIONS

CONTACT CARRIER MATERIAL	NYLON or PBT
CONTACT MATERIAL/PLATING	BRASS/GOLD
CONNECTOR HOUSING MATERIAL/PLATING	BRASS/NICKEL
GASKET	RUBBER (NBR or FPM)
RATED CURRENT [A]	3.0 A
RATED VOLTAGE [V]	150 V
OUTER JACKET MATERIAL/COLOR	PVC/YELLOW
CONDUCTOR INSULATION MATERIAL	PVC
NUMBER OF CONDUCTORS [AWG]	25x22 AWG
DRAIN/SHIELD	22 AWG DRAIN/POLYESTER FOIL SHIELD
PROTECTION CLASS	IEC IP67
TEMPERATURE	-40°C TO +105°C (-40°F TO +221°F)




CABLE LENGTH	TOLERANCE*
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER
STRIP LENGTH	TOLERANCE*
0-7mm	±0.5mm
8-29mm	±1.0mm
30-49mm	±2.0mm
50-69mm	±3.0mm
70-100mm	±4.0mm
OVER 100mm	±5.0mm
*UNLESS OTHERWISE SPECIFIED	

NOTES:

1."*" INDICATES LEAD LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.

SOURCE DRAWING - FOR REFERENCE ONLY

RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED. TURCK INC <i>High Technology Sensors and Automation Controls</i>		3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com			
							
MATERIAL	ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY	DRFT	JB	DATE	02/11/02	DESCRIPTION	DK 26-631-*
SEE SPECIFICATIONS		APVD	DD	SCALE	1=1.5		
FINISH		CONTACT TURCK FOR MORE INFORMATION	UNIT OF MEASUREMENT			IDENTIFICATION NO.	REV
SEE SPECIFICATIONS			MILLIMETER [INCH]				
		DO NOT SCALE THIS DRAWING			FILE: 777000982	SHEET 1 OF 1	

E	UPDATE RATED CURRENT SPECIFICATIONS	KMY	07/24/14	46464
REV	DESCRIPTION	BY	DATE	ECO NO.