

# Splitters

## 2-Branch Compact Splitter Part Number Key

Part Number Keys are to assist in IDENTIFICATION ONLY. Consult factory for catalog items not identified.

YBZ2 - [ ] - FSM 4.5 / 2 FK 4.5 - \* / \* / /S651

### Compact 2-Branch Splitter

YBZ2 = M12 Eurofast®  
YP2 = M8 Picofast®

### Housing Material

PX3 = 3 PNP LEDs  
PX2 = 2 PNP LEDs

### HomeRun Connector

FSM = Male Eurofast  
PSG = Male Picofast with cable  
RS = Male Eurofast with cable  
MFS = Male Picofast

### Number of HomeRun Wires

4.4 = 4 wires  
4.5 = 5 wires  
4M = 4 wires  
3M = 3 wires  
6M = 6 wires

### 2 Branch

### Wiring

(Blank) = Standard  
"/S651" = Parallel

### Cable Length in Meters

(Blank) = No cable

### Plug Options

(Blank) = No barb fitting  
T = "T" barb fitting (M12 Eurofast)

### Number of Branch Wires

4.5 = 5 wires  
3M = 3 wires  
4 = 3 wires  
4.4 = 4.4 wires  
4M = 4 wires

### Branch Connectors

FK = Female Eurofast connector  
PKG = Female Picofast connector with cable  
RK = Female Eurofast connector with cable  
MFK = Female Picofast connector  
PSG = Male Picofast connector with cable