

# Split Phase Hot Water Circulating Pump Open Drip Proof (ODP)



## APPLICATIONS:

Designed to meet manufacturer's requirements for use on hot water circulating pumps.

## FEATURES:

- Painted Red To Indicate Hot-Water Usage
- 40°C Ambient
- Reversible Rotation
- Resilient Hub Rings
- Special Balance For Quiet Operation
- Class B Insulation
- 1725 RPM
- Automatic Reset Thermal Overload Protector
- Sleeve Bearings Have All Angle Thrust System
- Units Match OEM Performance And Mechanical Features
- Sleeve Bearings Unless Noted
- 208v will not be marked on DOE regulated spread-voltage motors. Refer to online data
- Coupler assembly required for proper Bell & Gossett replacement

## Split Phase, NEMA<sup>®†</sup> Frame 48YZ

HP	Voltage	Catalog Number	List	Discount Symbol	Amps	Bolt Circle	Rings OC	SF	Rotation Shaft End	Ship Wt.	Notes	Industry Numbers
1/12	115	3255	\$252	DS-3HAC	2.5	4.63	5.94	1.75	CW	13		111034, 805316-010
1/6	115	3256	\$277	DS-3HAC	3.8	4.63	6.94	1.75	CW	15		111061, 817025-005
	115	3257	\$281	DS-3HAC	3.8	5.00	6.94	1.75	CW	14		111036, 111031, 817025-001
1/4	115	3259	\$312	DS-3HAC	4.6	5.00	6.94	1.25	CW	16		111040, 817025-007, 111050
1/3	115	3260	\$431	DS-3HAC	6.0	5.86	6.94	1.30	CCW	15		169226, 816141-002, 169038

## Capacitor Start, NEMA<sup>®†</sup> Frame 56YZ

HP	Voltage	Catalog Number	List	Discount Symbol	Amps	Bolt Circle	Rings OC	SF	Rotation Shaft End	Ship Wt.	Notes	Industry Numbers
1/2	115/208-230	3258	\$462	DS-3HAC	5.7/2.9-3.0	5.86	7.94	1.50	Rev	22		111044, 169228, 811757-001
3/4	115/208-230	3261	\$473	DS-3HAC	8.2/4.7-4.2	5.86	8.44	1.50	Rev	33		111047, 169230, 811757-002

